



Canon PGI-9G Green Ink Cartridge

Brand : Canon

Product code: 1041B001

Product name : PGI-9G Green Ink Cartridge



- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges†††
 - Genuine Canon Ink provides consistent quality prints 100% of the time†††
 - Genuine Canon Ink is 100% reliable so you can print with less stress†††
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PGI-9G Green Ink Cartridge

Canon PGI-9G Green Ink Cartridge:

The LUCIA ink range of professional inks deliver rich, high density colours excellent colour gamut and reliable quality. This pigment-based ink system offers outstanding photo permanence. The 14ml green ink tank allows you to print up to 765 photos in 10x15cm or 228 in A3+ size at ISO/IEC 24711† standard. Canon PGI-9G Green Ink Cartridge. Colour ink type: Pigment-based ink, Colour ink page yield: 765 pages, Printing colours: Green, Quantity per pack: 1 pc(s)

Features		Features	
Colour ink type	Pigment-based ink	Country of origin	Japan
Print technology	Inkjet printing	Colour	✓
Compatibility *	PIXMA Pro9500, PIXMA Pro9500 Mark II	Packaging data	
Quantity per pack *	1 pc(s)	Package width	135 mm
Colour ink page yield *	765 pages	Package depth	100 mm
Type *	Original	Package height	30 mm
Ink type	Pigment-based ink	Package weight	50 g
Printing colours *	Green	Logistics data	
		Harmonized System (HS) code	84439990



4960999357317

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.