

Epson Photo Quality Ink Jet Paper, DIN A3, 102g/m², 100 Sheets

Brand : Epson


Product code: C13S041068

Product name : Photo Quality Ink Jet Paper, DIN A3, 102g/m², 100 Sheets


Photo Quality Ink Jet Paper, DIN A3, 102g/m², 100 Sheets

Epson Photo Quality Ink Jet Paper, DIN A3, 102g/m², 100 Sheets:

With this white matt 102 g/m² hard paper, the printout resolution for the PhotReal® quality print is optimised up to 1440 dpi. Excellent for demanding commercial colour graphics, flyers, and posters. Epson Photo Quality Ink Jet Paper, DIN A3, 102g/m², 100 Sheets. Finish type: Matte, Media weight: 102 g/m², Paper size: A3. Width: 297 mm, Height: 420 mm. Quantity per pack: 1 pc(s), Package width: 310 mm, Package depth: 433 mm. Pallet width (UK): 100 cm, Pallet length (UK): 120 cm, Pallet height (UK): 148 cm. Country of origin: Japan



Features		Packaging data	
Paper size	A3	Package width	310 mm
Product colour	White	Package depth	433 mm
Finish type *	Matte	Package height	22 mm
Media weight *	102 g/m²	Package weight	1.55 kg
Sheets per pack	100 sheets	Logistics data	
Certification	Epson Stylus Color 3000, Epson Stylus Color 1520, Stylus Photo 1200, Stylus Color 1160, Stylus Photo 1270, Epson Stylus Pro 7000, Epson Stylus Pro 10000, Epson Stylus Photo 1290, Stylus Photo 1290 Silver, Stylus Photo R2400, Stylus Photo 1410, Stylus Photo R1900, Stylus Photo R2880, Stylus Office T1100, Stylus Photo R3000, WorkForce WF-7510, Stylus Photo R2000, Epson Artisan 1430, WorkForce WF-7520, WorkForce 7010, WorkForce WF-7620, WorkForce WF-7610, Expression Photo XP-950, Expression Photo XP-860, SureColor P600, SureColor P800, SureColor P405, Epson SureColor T3160 - 24", Epson SureColor T5160 - 36", Expression Premium XP-900, Epson SureColor T3460 - 24", Epson SureColor T5460 - 36", Expression Premium ET-7750, WorkForce WF-7710, WorkForce WF-7720, WorkForce WF-7725, Expression Photo HD XP-15000, SureColor T5460M - 36", Stylus Photo EX, Epson Stylus Pro 9000, Epson Stylus Pro 10600 DYE	Harmonized System (HS) code	37032000
		Pallet width (UK)	100 cm
		Pallet length (UK)	120 cm
		Pallet height (UK)	148 cm
		Pallet gross width	80 cm
		Pallet gross length	120 cm
		Pallet gross height	148 cm
		Products per pallet	300 pc(s)
		Products per pallet (UK)	280 pc(s)
		Products per pallet layer	50 pc(s)
Weight & dimensions		Products per pallet layer (UK)	60 pc(s)
		Master (outer) case width	336 mm
		Master (outer) case length	456 mm
		Master (outer) case height	247 mm
		Master (outer) case gross weight	17.3 g
		Products per master (outer) case	10 pc(s)
		Other features	
		Country of origin	Japan
Packaging data			
Quantity per pack	1 pc(s)		



0010343812031



010343812031

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.