

Epson Iron-on-Transfer Paper - A4 - 10 Sheets

Brand : EpsonProduct code: C13S041154

Product name : Iron-on-Transfer Paper - A4 - 10 Sheets

Iron-on-Transfer Paper - A4 - 10 Sheets

Epson Iron-on-Transfer Paper - A4 - 10 Sheets:


Creative customisation
Get creative with our easy to use iron-on transfer paper. Bring photos, graphics and text to life by ironing this transfer paper on to almost any light coloured cotton. You can create personalised gifts for your family, party favours such as T-shirts, or your very own slogan bag - the choice is yours.

Printing is a partnership
Enjoy vivid colours, beautiful tones and incredible detail when you combine Epson's papers and inks. This paper has been specially developed to work with Epson's range of inks and printers to deliver the best possible quality.

Great for every printer
Our papers produce great results with other manufacturers' printers and inks so everyone can take advantage of Epson's expertise.



Features		Logistics data	
Compatible products	StylusColor 400 600 800 850 900 Photo700 Photo750 PhotoEX	Master (outer) case width	238 mm
Weight & dimensions		Master (outer) case height	330 mm
		Products per pallet	2000 pc(s)
Print media weight	124 g/m²	Pallet gross length	120 cm
Paper dimensions	210 mm x 297 mm	Pallet gross width	80 cm
Packaging data		Pallet gross height	132 cm
		Minimum order quantity	50 pc(s)
Package width	243 mm	Products per master (outer) case	50 pc(s)
Package depth	354 mm	Products per pallet layer	500 pc(s)
Package height	6 mm	Products per pallet layer (UK)	650 pc(s)
Package weight	300 g	Products per pallet (UK)	2400 pc(s)
Quantity per pack *	1 pc(s)	Pallet length (UK)	120 cm
Logistics data		Pallet width (UK)	100 cm
		Pallet height (UK)	132 cm
Master (outer) case gross weight	15 g		
Master (outer) case length	344 mm		



0010343814400



010343814400

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.