



Canon PGI-9MBK Matte Black Ink Cartridge

Brand : Canon **Product code:** 10338001

Product name : PGI-9MBK Matte Black Ink Cartridge



- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges†††
 - Genuine Canon Ink provides consistent quality prints 100% of the time†††
 - Genuine Canon Ink is 100% reliable so you can print with less stress†††
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PGI-9MBK Matte Black Ink Cartridge

Canon PGI-9MBK Matte Black Ink Cartridge:

The LUCIA ink range of professional inks deliver rich, high density colours excellent colour gamut and reliable quality. This pigment-based ink system offers outstanding photo permanence. The 14ml matte black ink tank allows you to print up to 845 photos in 10x15cm or 167 in A3+ size at ISO/IEC 24711† standard.

Canon PGI-9MBK Matte Black Ink Cartridge. Colour ink type: Pigment-based ink, Printing colours: Matte black, Quantity per pack: 1 pc(s), Black ink page yield: 845 pages

Features		Features	
Colour ink type	Pigment-based ink	Colour	×
Print technology	Inkjet printing	Packaging data	
Compatibility *	DELL PIXMA PRO 9500	Package width	170 mm
Quantity per pack *	1 pc(s)	Package depth	140 mm
Black ink page yield *	845 pages	Package height	20 mm
Type *	Original	Package weight	100 g
Ink type	Pigment-based ink	Package type	Blister
Printing colours *	Matte black	Logistics data	
Country of origin	Japan	Harmonized System (HS) code	84439990



4960999357157



0999992482898



999992482898

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.