

Epson Turtle T1579 Light Light Black

Brand : EpsonProduct family: TurtleProduct code: C13T15794010

Product name : T1579 Light Light Black

- Excellent colour stability
 - Exceptional light-fastness
 - Excellent black and white image quality with three levels of black
- T1579 Light Light Black

Epson Turtle T1579 Light Light Black:

Epson UltraChrome K3 inks are well known for their wide gamut and accurate colour rendition with virtually no colour twist. Now, with the addition of newly formulated vivid magenta and vivid light magenta inks, they offer an even wider colour gamut with a dramatically improved range of expression. Epson Turtle T1579 Light Light Black. Colour ink type: Pigment-based ink, Cartridge capacity: High (XL) Yield, Black ink volume: 25.9 ml, Printing colours: Light light black, Quantity per pack: 1 pc(s), Black ink page yield: 23000 pages



Features		Packaging data	
Colour ink type	Pigment-based ink	Package depth	142 mm
Print technology	Inkjet printing	Package height	113 mm
Compatibility *	- Epson Stylus Photo R3000	Package type	Blister
Quantity per pack *	1 pc(s)	Logistics data	
Black ink cartridges quantity	1	Pallet gross width	80 cm
Black ink volume	25.9 ml	Pallet gross length	120 cm
Black ink page yield *	23000 pages	Pallet gross height	48 cm
Type *	Original	Products per pallet	2400 pc(s)
Cartridge capacity	High (XL) Yield	Harmonized System (HS) code	84439990
Ink type	Pigment-based ink	Pallet width (UK)	100 cm
Printing colours *	Light light black	Pallet length (UK)	120 cm
Brand compatibility *	Epson	Pallet height (UK)	48 cm
OEM code	C13T15794010	Products per pallet (UK)	2400 pc(s)
Country of origin	China	Products per pallet layer	240 pc(s)
Packaging data		Products per pallet layer (UK)	240 pc(s)
Package width	30 mm	Minimum order quantity	8 pc(s)



8715946488035




3610170025603




5053676857848



8715946479514




5053973165592



9082014022958



5052217525956



4053162273788



5054533337138

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.