

StarTech.com 2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch

Brand : StarTech.com

Product code: SV211USB

Product name : 2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch



StarTech.com 2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch - KVM with VGA - Dual Port VGA KVM Switch

StarTech.com 2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch. Keyboard port type: USB, Mouse port type: USB, Video port type: VGA. Maximum resolution: 2048 x 1536 pixels, Maximum digital resolution: 2048 x 1536 pixels. Product colour: Black, Housing material: Plastic, Cable length: 0.85 m. Windows operating systems supported: Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64,..., Mac operating systems supported: Mac OS 9.0, Mac OS 9.1, Mac OS 9.2, Mac OS X 10.0 Cheetah, Mac OS X 10.1 Puma, Mac OS X 10.2..., Server operating systems supported: Windows Server 2003, Windows Server 2008 R2, Windows Server 2012, Windows Server 2016, Windows.... Compliance certificates: RoHS

Ports & interfaces		System requirements	
Number of computers controlled *	2	Mac operating systems supported	Mac OS 9.0, Mac OS 9.1, Mac OS 9.2, Mac OS X 10.0 Cheetah, Mac OS X 10.1 Puma, Mac OS X 10.2 Jaguar, Mac OS X 10.3 Panther, Mac OS X 10.4 Tiger, Mac OS X 10.5 Leopard, Mac OS X 10.6 Snow Leopard, Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Keyboard port type *	USB		
Mouse port type *	USB		
Video port type *	VGA		
Console ports *	USB A, VGA (D-Sub)		
Console USB ports quantity	2		
Audio connections	✗		
Performance		Server operating systems supported	Windows Server 2003, Windows Server 2008 R2, Windows Server 2012, Windows Server 2016, Windows Server 2019
Maximum resolution *	2048 x 1536 pixels		
Maximum digital resolution	2048 x 1536 pixels		
Hot-Plug support	✓		
Daisy chain	✗	Sustainability	
		Compliance certificates	RoHS
Design		Operational conditions	
Rack mounting *	✗	Operating temperature (T-T)	0 - 40 °C
Product colour *	Black	Storage temperature (T-T)	-20 - 60 °C
Housing material	Plastic	Operating relative humidity (H-H)	0 - 90%
Cable length	0.85 m	Weight & dimensions	
LED indicators	✓	Width	66 mm
Certification	CE, FCC	Depth	88 mm
Display		Height	23 mm
Built-in display *	✗	Weight	380 g
Power		Packaging data	
USB powered	✓	Package width	164 mm
		Package depth	250 mm
		Package height	63 mm
		Package weight	435 g

System requirements		Packaging content	
Windows operating systems supported	Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 Pro, Windows 10 Pro x64, Windows 2000, Windows 2000 Professional, Windows 7, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 7 x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8 x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows Vista x64, Windows XP, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64	Manual	✓
		Other features	
		Audio support	✓
		IP control	✗
		Logistics data	
		Harmonized System (HS) code	85176200



0065030858625



065030858625



5054242255051

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.