



Canon PGI-72CO Clear Ink Cartridge (Chroma Optimiser)

Brand : CanonProduct code: 6411B001

Product name : PGI-72CO Clear Ink Cartridge (Chroma Optimiser)



- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges†††
 - Genuine Canon Ink provides consistent quality prints 100% of the time†††
 - Genuine Canon Ink is 100% reliable so you can print with less stress†††
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- PGI-72CO Clear Ink Cartridge (Chroma Optimiser)

Canon PGI-72CO Clear Ink Cartridge (Chroma Optimiser):

The Chroma Optimizer clear ink from the professional LUCIA ink range delivers uniform glossiness, expands colour gamut and makes the black colours deeper. This pigment-based clear ink is applied on top of the colour inks. The 14ml ink tank allows you to print up to 165 photos in 10x15cm or 31 in A3+ size at at ISO/IEC 29102† standard.

Canon PGI-72CO Clear Ink Cartridge (Chroma Optimiser). Cartridge capacity: Standard Yield, Colour ink page yield: 165 pages, Quantity per pack: 1 pc(s)

Features		Operational conditions	
Print technology	Inkjet printing	Operating relative humidity (H-H)	5 - 95%
Compatibility *	Canon PIXMA PRO-10	Storage temperature (T-T)	10 - 35 °C
Quantity per pack *	1 pc(s)	Operating temperature (T-T)	15 - 35 °C
Colour ink page yield *	165 pages	Storage relative humidity (H-H)	5 - 95%
Type *	Original	Packaging data	
Cartridge capacity	Standard Yield	Package type	Blister
Brand compatibility *	Canon	Other features	
Country of origin	Japan	Page yield footnote	10x15cm, ISO/IEC 24734
Colour	✓	Logistics data	
		Harmonized System (HS) code	84439990



4960999902326



9102014022656

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.