

ZYXEL

Zyxel SFP10G-LR network transceiver module Fiber optic 10000 Mbit/s SFP+ 1310 nm

Brand : Zyxel
Product name : SFP10G-LR
Product code: SFP10G-LR-ZZ0101F

SFP10G-LR, SFP Plus Transceiver

Zyxel SFP10G-LR network transceiver module Fiber optic 10000 Mbit/s SFP+ 1310 nm:

- Hot-Pluggable with Maximum Flexibility
- Low Power Dissipation
- Industry Standard Compliance
- SFP MSA (Multi-Source Agreement) Compliance
- Compact Size, High Port Density

Zyxel SFP10G-LR. SFP transceiver type: Fiber optic, Maximum data transfer rate: 10000 Mbit/s, Interface type: SFP+. Width: 14.8 mm, Depth: 56.5 mm, Height: 11.8 mm. Quantity per pack: 1 pc(s)



Performance		Features	
SFP transceiver type *	Fiber optic	Hot-Plug support	✓
Maximum data transfer rate *	10000 Mbit/s	Weight & dimensions	
Interface type *	SFP+	Width	14.8 mm
Single-mode fiber (SMF) supported	✓	Depth	56.5 mm
Fiber optic connector	SFP+	Height	11.8 mm
Maximum transfer distance	10000 m	Weight	20 g
Wavelength	1310 nm	Packaging content	
Fiber ports quantity	2	Quantity per pack	1 pc(s)
		Logistics data	
		Harmonized System (HS) code	85369010



4718937567652



4052305858073

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.