

Epson Ultrasmooth Fine Art Paper, A3+, 325g/m², 25 Blatt

Brand : Epson

Product code: C13S041896

Product name : Ultrasmooth Fine Art Paper, A3+, 325g/m², 25 Blatt



Ultrasmooth Fine Art Paper, A3 , 325g/m², 25 Blatt

Epson Ultrasmooth Fine Art Paper, A3+, 325g/m², 25 Blatt:

Artists and professional photographers require true archival print media in a variety of weights and surface textures for their digital fine art and photography. Now Epson brings you an acid free, 100% cotton hot press paper that is coated on both sides for extra versatility. This cylinder mould-made product, features an ultra smooth finish on two sides (sheets) that is optimised for our photographic dye, Epson UltraChrome and Archival Inks. Offered in a variety of sizes and formats, this fine art paper is not only acid, lignin and chlorine free, it is also buffered with calcium carbonate for a true archival sheet. Like all Epson's innovative media, this paper is engineered to give you the highest resolution and colour saturation possible.

Epson Ultrasmooth Fine Art Paper, A3+, 325g/m², 25 Blatt. Roll width: 32.9 cm, Finish type: Matt, Printing media thickness: 460 µm, Print media weight: 325 g/m²

Features		Logistics data	
Roll width *	32.9 cm	Pallet gross length	120 cm
Printing media thickness	460 µm	Pallet gross width	80 cm
Print media weight *	325 g/m²	Pallet gross height	114 cm
Finish type *	Matt	Products per master (outer) case	4 pc(s)
Country of origin	Taiwan	Products per pallet layer	8 pc(s)
Packaging data		Products per pallet layer (UK)	12 pc(s)
Quantity per pack	1 pc(s)	Products per pallet (UK)	120 pc(s)
Package width	395 mm	Pallet length (UK)	120 cm
Package depth	595 mm	Pallet width (UK)	100 cm
Package weight	2.46 kg	Pallet height (UK)	114 cm
Package height	20 mm	Harmonized System (HS) code	48025590
Logistics data		Other features	
Master (outer) case gross weight	8.1 g	Products per pallet	80 pc(s)
Master (outer) case length	620 mm	Media size (1 slide)	A3+
Master (outer) case width	406 mm	Media sheets per package	25 sheets
Master (outer) case height	114 mm		



0010343849365



010343849365

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.