

Targus numeric keypad Black, Grey

Brand : Targus

Product code: AKP10EU

Product name : Numeric Keypad

Numeric Keypad

Targus numeric keypad Black, Grey:

The Targus Numeric Keypad allows users to type numbers into spreadsheets and other applications quickly and easily. The full-size 19mm concave keys improve speed and accuracy by making it easier to locate and press the numbers you are looking for. The integrated ergonomic tilt provides added comfort which helps reduce wrist strain after a long work day. The USB cord is 91 cm long to provide additional flexibility in the workspace. Ideal for in office or in home use.

- Functionality - Full sized concave keys are comfortable and large for increased accuracy; great for those working on spreadsheets, accounting files and financial applications.
- Ergonomic - Ergonomic tilt provides support to help prevent wrist strain.
- Easy to use - USB port required; True plug & play device, no drivers required.
- Compatibility - PC, Mac and Netbook compatible.

Targus Numeric Keypad. Cable length: 0.91 m, Product colour: Black, Grey. Weight: 130 g



Design		Logistics data	
Cable length	0.91 m	Products per shipping (inner) case	4 pc(s)
Product colour *	Black, Grey	Shipping (inner) case width	15.2 cm
Weight & dimensions		Shipping (inner) case length	22.4 cm
Width	84 mm	Shipping (inner) case height	16.5 cm
Depth	125 mm	Shipping (inner) case net weight	880 g
Height	28 mm	Products per master (outer) case	16 pc(s)
Weight	130 g	Master (outer) case width	320 mm
Packaging data		Master (outer) case length	460 mm
Package width	70 mm	Master (outer) case height	185 mm
Package depth	210 mm	Master (outer) case gross weight	4.03 kg
Package height	153 mm	Products per pallet	800 pc(s)
Package weight	200 g		
Logistics data			
Harmonized System (HS) code	84733080		



5054629108048



5051794002799

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.