

Targus CN600 backpack Black Nylon, Polyester

Brand : Targus

Product code: CN600EU

Product name : CN600

- Removable padded notebook compartment for screens up to 15.6"
- Hard wearing nylon exterior with large zippers
- Adjustable fasteners on each side of the backpack ensuring improved comfort
- Internal divider for work papers for your day out of the office
- Side mesh pockets


Classic, 15.6", 20 L, 387 x 25 x 265 mm, 310 x 175 x 470 mm, 880 g

Targus CN600 backpack Black Nylon, Polyester:

This Backpack appeals to today's mobile professionals with an active lifestyle and a more casual work environment. Combining convenience and comfort with attractive design, it offers efficient storage for your notebook computer and mobile accessories. The removable notebook compartment (fits 15.4 - 16 inch laptops) is fully cushioned and has a security fastener ensuring your notebook stays firmly in place. Functional solution at the best price.




Features		Weight & dimensions	
Product main colour *	Black	Volume	20 L
Style	City	Notebook compartment dimensions (W x D x H)	265 x 25 x 387 mm
Coloration	Monochromatic	Packaging data	
Recommended gender	Unisex	Package width	360 mm
Notebook compartment	✓	Package depth	110 mm
Tablet compartment	✓	Package height	480 mm
Minimum screen size	39.1 cm (15.4")	Package weight	940 g
Maximum screen size	40.6 cm (16")	Material	
Exterior pockets	Front pocket, Side pocket	Material *	Nylon, Polyester
Zipper pocket(s)	✓	Logistics data	
Handle(s)	✓	Products per pallet	85 pc(s)
Carrying handle(s)	✓	Harmonized System (HS) code	42029291
Closure type	Zipper	Master (outer) case width	415 mm
Country of origin	CHN	Master (outer) case length	500 mm
Weight & dimensions		Master (outer) case height	360 mm
Width *	171.5 mm	Master (outer) case gross weight	5.98 kg
Depth *	310 mm	Products per master (outer) case	5 pc(s)
Height *	480 mm		
Weight	850 g		



5024442932205



5051964164241



5546213694254

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.