

Epson LQ-630 dot matrix printer 360 cps

Brand : Epson

Product code: C11C480141A0

Product name : LQ-630



Impact dot matrix, 24 pins, 80 columns, 24 Needles, 360x180 DPI, USB 2.0, Parallel, 20W, 3.5 kg

Epson LQ-630 dot matrix printer 360 cps:

LQ-630 is a small and reliable printer especially for counter application. With its small design with 80 columns, LQ-630 fits perfectly in environments where space is rather limited. The ejection of both, continuous paper and cut sheets at front side enables easy handling of the print outs only at the front side of the printer. Due to the printer's flatbed technology, LQ-630 can print even smallest cut sheet forms and stickers down to 9 cm x 7 cm. LQ-630 can ideally be used with retail stores, banks, post offices, doctors' surgeries, ticket shops, cinemas, pizza services. Moreover the printer is perfect for label and protocol printing with trade industrial firms.

Printing		Power	
Maximum printing width (columns) *	80	AC input voltage	220 - 240 V
Colour *	✗	Operational conditions	
Maximum print speed *	360 cps	Operating temperature (T-T)	5 - 35 °C
Maximum number of copies	5 copies	Operating relative humidity (H-H)	10 - 80%
Built-in barcodes	Code 39, POSTNET, UPC-A, UPC-E	Weight & dimensions	
Paper handling		Width	386 mm
Maximum print size	254 x 559 mm	Depth	306 mm
Features		Height	185 mm
Product colour *	Grey	Weight	3.5 kg
Buffer size *	32 KB	Packaging data	
Sound pressure level (printing) *	57 dB	Quantity per pack	1 pc(s)
Country of origin	China	Package width	310 mm
Ports & interfaces		Package depth	455 mm
Standard interfaces *	Parallel, USB 2.0	Package height	265 mm
Endurance		Package weight	5.2 kg
Print head *	24-pin	Logistics data	
Print head life	200 million characters	Products per pallet	35 pc(s)
Ribbon life	2 million characters	Pallet gross width	120 cm
Mean time between failures (MTBF)	6000 h	Pallet gross height	100 cm
Power		Products per pallet layer	5 pc(s)
Power consumption (typical)	20 W	Products per pallet layer (UK)	7 pc(s)
Power consumption (standby)	4.8 W	Products per pallet (UK)	49 pc(s)
		Pallet length (UK)	2 m



8715946540566

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.