

ASUS STRIX SOAR Internal 7.1 channels PCI-E

Brand : ASUS

Product code: 90YB00J0-M1UA00

Product name : STRIX SOAR

- 116dB signal-to-noise ratio (SNR) and audiophile-grade DAC: Enjoy high-fidelity, immersive sound
 - Sonic Studio utility: Take full control over loads of sound technologies via an intuitive, one-page interface
 - Sonic Radar Pro: Lets you pinpoint the exact location of in-game sounds and enhances critical audio details like enemy footsteps for an aural advantage
 - 600ohm headphone amplifier: For enhanced bass and clear, detailed sound
- 7.1 PCI Express, 384KHz / 24bit, 116 dB

ASUS STRIX SOAR. Audio output channels: 7.1 channels, Audio quality: 24 bit, Line-out Signal-to-Noise Ratio (SNR): 116 dB. Host interface: PCI-E. Cables included: S/PDIF. Windows operating systems supported: Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic x64, Windows 7 Home Premium,..... Width: 130 mm, Depth: 190 mm, Height: 22 mm



Audio		Ports & interfaces	
Internal *	✓	Host interface *	PCI-E
Audio quality *	24 bit	Line-in	✓
Audio output channels *	7.1 channels	Line-out	✓
Line-out Signal-to-Noise Ratio (SNR) *	116 dB	Headphone outputs	1
Line-in Signal-to-Noise Ratio (SNR)	110 dB	S/PDIF out port	✓
Audio A/D Converter (ADC)	24-bit/192kHz	Features	
Digital-to-Analog Conversion (DAC)	24-bit/192kHz	Cables included	S/PDIF
Line-in Total Harmonic Distortion (THD)	0.000316%	Software	
Line-out Total Harmonic Distortion (THD)	0.001%	Windows operating systems supported	Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64
Frequency range	10 - 48000 Hz		
		Weight & dimensions	
		Width	130 mm
		Depth	190 mm
		Height	22 mm
		Logistics data	
		Harmonized System (HS) code	84733020



4712900005974

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.