

Epson Padlock Singlepack Cyan 35 DURABrite Ultra Ink

Brand : EpsonProduct family: PadlockProduct code: C13T35824010

Product name : Singlepack
Cyan 35 DURABrite Ultra Ink

Singlepack Cyan 35 DURABrite Ultra Ink
Epson Padlock Singlepack Cyan 35 DURABrite Ultra Ink. Cartridge capacity: Standard Yield, Colour ink
page yield: 650 pages, Colour ink volume: 9.1 ml, Printing colours: Cyan, Quantity per pack: 1 pc(s)



Features		Logistics data	
Print technology	Inkjet printing	Pallet gross width	80 cm
Compatibility *	- WorkForce Pro WF-4740DTWF -	Pallet gross length	120 cm
	WorkForce Pro WF-4730DTWF -	Pallet gross height	2 m
Quantity per pack *	WorkForce Pro WF-4725DWF -	Products per pallet	2400 pc(s)
	WorkForce Pro WF-4720DWF	Pallet gross weight	0 g
Colour ink cartridges quantity	1 pc(s)	Master (outer) case width	120 mm
Colour ink volume	9.1 ml	Master (outer) case length	260 mm
Colour ink page yield *	650 pages	Master (outer) case height	146 mm
Type *	Original	Products per master (outer) case	8 pc(s)
Cartridge capacity	Standard Yield	Master (outer) case gross weight	0 g
Printing colours *	Cyan	Master (outer) case GTIN (EAN/UPC)	8715946632711
Brand compatibility *	Epson	Harmonized System (HS) code	84439990
OEM code	C13T35824010	Pallet width (UK)	100 cm
Country of origin	Indonesia	Pallet length (UK)	120 cm
Packaging data		Pallet height (UK)	2 m
Package width	120 mm	Pallet weight (UK)	0 g
Package depth	260 mm	Products per pallet (UK)	2400 pc(s)
Package height	146 mm	Products per pallet layer	240 pc(s)
Package weight	58 g	Products per pallet layer (UK)	240 pc(s)
Package type	Blister	Minimum order quantity	8 pc(s)
Other features			
Certification	CE		



8715946632278



4058154209158



5057454666899

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.