



TP-Link TL-SG1005D network switch Unmanaged Gigabit Ethernet (10/100/1000) Black

Brand : TP-Link

Product code: TL-SG1005D

Product name : TL-SG1005D

- 5 Gigabit Auto-Negotiation RJ45 ports, Supports Auto MDI / MDIX
- Green Ethernet technology saves the power up to 85%
- IEEE 802.3x flow control provides reliable data transfer
- Plastic case, desktop or wall-mounting design
- Plug and play, no configuration required

5 10/100/1000Mbps RJ45 Ports, AUTO Negotiation/AUTO MDI/MDIX, 140 x 88 x 23 mm, 220V/50Hz
TP-Link TL-SG1005D. Switch type: Unmanaged. Basic switching RJ-45 Ethernet ports type: Gigabit Ethernet (10/100/1000), Basic switching RJ-45 Ethernet ports quantity: 5. Full duplex. MAC address table: 8000 entries, Switching capacity: 10 Gbit/s. Networking standards: IEEE 802.3, IEEE 802.3ab, IEEE 802.3u, IEEE 802.3x. Power connector: DC-in jack




Management features		Design	
Switch type *	Unmanaged	Rack mounting *	✗
Ports & interfaces		Product colour	Black
Basic switching RJ-45 Ethernet ports quantity *	5	LED indicators	✓
Basic switching RJ-45 Ethernet ports type *	Gigabit Ethernet (10/100/1000)	Power	
Gigabit Ethernet (copper) ports quantity	5	Power source *	DC
Power connector	DC-in jack	Input current	0.6 A
Network		Input voltage	9 V
Networking standards *	IEEE 802.3, IEEE 802.3ab, IEEE 802.3u, IEEE 802.3x	Power consumption (max)	2.41 W
Full duplex	✓	Power over Ethernet (PoE)	
Half duplex	✓	Power over Ethernet (PoE) *	✗
Flow control support	✓	Operational conditions	
Auto MDI/MDI-X	✓	Operating temperature (T-T)	0 - 40 °C
Auto-negotiation	✓	Storage temperature (T-T)	-40 - 70 °C
MAC address auto-learning supported	✓	Operating relative humidity (H-H)	10 - 90%
MAC address auto-aging supported	✓	Storage relative humidity (H-H)	5 - 90%
Data transmission		Heat dissipation	8.22 BTU/h
Supported data transfer rates	10/100/1000 Mbit/s	Weight & dimensions	
Switching capacity *	10 Gbit/s	Width	165 mm
MAC address table *	8000 entries	Depth	108 mm
Store-and-forward	✓	Height	28 mm
Maximum data transfer rate	1 Gbit/s	Packaging content	
Jumbo frames support	✓	Quick start guide	✓
Jumbo frames	15000	Packaging data	
		Package width	145 mm
		Package depth	108 mm
		Package height	85 mm
		Package weight	240 g



6935364020255



1210002616553



0840460606684



840460606684

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.