

Epson LQ-2190 dot matrix printer 576 cps

Brand : Epson

Product code: C11CA92001A0

Product name : LQ-2190



LQ-2190 - 576cps; parallel & USB 2.0; 54dB
Epson LQ-2190. Maximum print speed: 576 cps. Buffer size: 128 KB, Sound pressure level (printing): 54 dB, Country of origin: Indonesia. Print direction: Bidirectional, Print head life: 400 million characters, Ribbon life: 15 million characters. Power consumption (typical): 46 W. Weight: 13 kg

Printing		Packaging data	
Colour *	×	Package weight	15.5 kg
Maximum print speed *	576 cps	Other features	
Features		Dimensions (WxDxH)	639 x 402 x 256 mm
Buffer size *	128 KB	Power requirements	240V
Sound pressure level (printing) *	54 dB	Connectivity technology	Wired
Country of origin	Indonesia	Print technology	Dot matrix
Endurance		Compatible operating systems	Microsoft Windows 2000/XP/Vista/7
Print direction	Bidirectional	Technical details	
Print head life	400 million characters	Sustainability certificates	ENERGY STAR
Ribbon life	15 million characters	Logistics data	
Power		Products per pallet	14 pc(s)
Power consumption (typical)	46 W	Pallet gross length	120 cm
Weight & dimensions		Pallet gross width	80 cm
Weight	13 kg	Pallet gross height	2.21 m
Packaging data		Products per pallet layer	2 pc(s)
Quantity per pack	1 pc(s)	Products per pallet layer (UK)	2 pc(s)
Package width	520 mm	Products per pallet (UK)	14 pc(s)
Package depth	750 mm	Pallet length (UK)	120 cm
Package height	295 mm	Pallet width (UK)	100 cm
		Pallet height (UK)	2.21 m



8715946468266

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.