

StarTech.com 20g Tube CPU Thermal Paste Grease Compound for Heatsinks

Brand : StarTech.com

Product code: HEATGREASE20

Product name : 20g Tube CPU Thermal Paste Grease Compound for Heatsinks



StarTech.com 20g Tube CPU Thermal Paste Grease Compound for Heatsinks - heat grease - cpu paste - thermal compound

[StarTech.com 20g Tube CPU Thermal Paste Grease Compound for Heatsinks:](#)

The HEATGREASE20 CPU Thermal Paste Compound can be used to improve the effectiveness of a CPU cooler, by thermally bonding the surface of the CPU to the heatsink, which enables the heatsink and fan to work more efficiently to remove harmful heat from the CPU.

This 20g tube of ceramic-based thermal grease is enough for a large number of CPU installations for most home or business computers or any other light application where good thermal bonding between two surfaces is required.

Please see our support section for the Material Safety Data Sheet for HEATGREASE20.

The StarTech.com Advantage

- Improves the heat transfer between a CPU and heatsink to keep the CPU running cooler
- Effectively fills surface imperfections on CPU to prevent air pockets and help heat transfer
- Ceramic-based compound that is electrically non-conductive, for safe use around electronics

Features		Technical details	
Thermal conductivity	1.066 W/m·K	Compliance certificates	RoHS
Product colour	White	Weight & dimensions	
Thermal resistance	0.195 °C/W	Width	72 mm
Specific gravity	2.3 g/cm ³	Depth	18 mm
Operating temperature (T-T)	-20 - 100 °C	Height	18 mm
Storage temperature (T-T)	-50 - 100 °C	Weight	24 g
Operating relative humidity (H-H)	10 - 80%	Packaging data	
Technical details		Package width	84 mm
Evaporation (@ 200°C/24h)	0.001%	Package depth	152 mm
Bleed (@ 200°C/24h)	0.005%	Package height	23 mm
		Package weight	37 g



0065030844826



065030844826



5054629277829

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.