



Canon CLI-581C Cyan Ink Cartridge

Brand : Canon
Product code: 2103C001

Product name : CLI-581C Cyan Ink Cartridge



- ChromaLife100 system ensuring long-lasting print quality
 - Used for both photos and documents
 - Rich, vivid colour printing
 - Affordable price
 - Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges²
 - Genuine Canon Ink provides consistent quality prints 100% of the time²
 - Genuine Canon Ink is 100% reliable so you can print with less stress²
 - Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- CLI-581C Cyan Ink Cartridge

Canon CLI-581C Cyan Ink Cartridge:

This Cyan ink is used for printing high quality colour photos. Combined with Canon's photo paper it protects your images from fading using the ChromaLife100 system. Easily replaceable 5.6ml ink cartridge, print up to 250 pages with cyan at ISO/IEC 24711¹ standard.

Canon CLI-581C Cyan Ink Cartridge. Colour ink page yield: 250 pages, Colour ink volume: 5.6 ml, Printing colours: Cyan

Features		Features	
Compatibility *	PIXMA TS8152 PIXMA TS8151 PIXMA TR7550 PIXMA TS6151 PIXMA TS9155 PIXMA TS9150 PIXMA TS6150 PIXMA TR8550 PIXMA TS8150	Brand compatibility *	Canon
		OEM code	CLI-581C
		Country of origin	Japan
		Packaging data	
		Package width	96 mm
Colour ink cartridges quantity	1	Package depth	112 mm
Colour ink volume	5.6 ml	Package height	22 mm
Colour ink page yield *	250 pages	Package weight	34 g
Type *	Original	Logistics data	
Printing colours *	Cyan	Harmonized System (HS) code	84439990



4549292087086

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.