



Canon CLI-581XL Magenta Ink Cartridge

Brand : Canon

Product code: 2050C001

Product name : CLI-581XL Magenta Ink Cartridge

- ChromaLife100 system ensuring long-lasting print quality
- Used for both photos and documents
- Rich, vivid colour printing
- Affordable price
- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges²
- Genuine Canon Ink provides consistent quality prints 100% of the time²
- Genuine Canon Ink is 100% reliable so you can print with less stress²
- Return every ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.

CLI-581XL Magenta Ink Cartridge

[Canon CLI-581XL Magenta Ink Cartridge:](#)

This 8.3ml high yield magenta ink is used for printing high quality documents and photos. It has a larger tank capacity meaning better value and twice the amount of printing compared to the standard equivalent. Combined with Canon's photo paper it protects your images from fading using the ChromaLife100 system, print up to 225 photos with magenta XL cartridge at ISO/IEC 29102¹ standard.

Features		Features	
Colour ink type	Pigment-based ink	Printing colours *	Magenta
Compatibility *	PIXMA TR8550 PIXMA TS6151 PIXMA TS8150 PIXMA TS8151 PIXMA TS9155 PIXMA TR7550 PIXMA TS8152 PIXMA TS9150 PIXMA TS6150	Brand compatibility *	Canon
		OEM code	CLI-581M XL
		Country of origin	Japan
		Packaging data	
Colour ink cartridges quantity	1	Package width	96 mm
Colour ink volume	8.3 ml	Package depth	110 mm
Colour ink page yield *	225 pages	Package height	22 mm
Type *	Original	Package weight	40 g
Ink type	Pigment-based ink	Logistics data	
		Harmonized System (HS) code	84439990





4549292087024

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.