

StarTech.com 100cm Serial Attached SCSI SAS Cable - SFF-8087 to SFF-8087

Brand : StarTech.com

Product code: SAS8787100

Product name : 100cm Serial Attached SCSI SAS Cable - SFF-8087 to SFF-8087

StarTech.com 100cm Serial Attached SCSI SAS Cable - SFF-8087 to SFF-8087

StarTech.com 100cm Serial Attached SCSI SAS Cable - SFF-8087 to SFF-8087:


Provide durable connectivity for high-performance networks, servers, workstations and desktops

The SAS8787100 1-meter Internal Mini-SAS cable (with Sidebands) features two SFF-8087 connectors, helping you transmit, manage and protect critical data and digital content.

Designed to provide durable connectivity for high-performance networks, servers, workstations and desktops, this Mini-SAS cable is backed by StarTech.com's Lifetime Warranty.

The StarTech.com Advantage

- Confidently transmit, manage and protect critical data and digital content
 - Easy to use and install
 - Backed by StarTech.com lifetime warranty
- StarTech.com 100cm Serial Attached SCSI SAS Cable - SFF-8087 to SFF-8087. Cable standard: Ultra-640 SCSI, Cable type: External, Cable length: 1 m. Certification: RoHS, CE, REACH. Weight: 51.8 g. Package width: 17 mm, Package depth: 138 mm, Package height: 280 mm




Features		Certificates	
Product colour *	Black	Certification	RoHS, CE, REACH
Cable standard *	Ultra-640 SCSI	Weight & dimensions	
Cable type *	External	Weight	51.8 g
Cable length *	1 m	Packaging data	
Connector 1 *	SFF-8087	Package width	17 mm
Connector 2 *	SFF-8087	Package depth	138 mm
Connector gender	Male/Male	Package height	280 mm
Number of connectors	2	Package weight	51.8 g



0065030826495



065030826495



0617407478952



617407478952

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.