



Lenovo D3284 disk array 0 TB Rack (5U) Black

Brand : Lenovo

Product code: 6413E5F

Product name : D3284



D3284, 3x 12Gbps SAS x4, RAID, 5U


Lenovo D3284 disk array 0 TB Rack (5U) Black:

The Lenovo Storage D3284 High Density Expansion Enclosure offers 12 Gbps SAS direct-attached storage expansion capabilities that are designed to provide density, speed, scalability, security, and high availability for medium to large businesses. The D3284 delivers enterprise-class storage technology in a cost-effective dense solution with flexible drive configurations of up to 84 drives in 5U and RAID or JBOD (non-RAID) host connectivity.

This product guide provides essential pre-sales information to understand the structure of the D3284 drive enclosure offering, its key features and specifications, components and options, and configuration guidelines.

This guide is intended for technical specialists, sales specialists, sales engineers, IT architects, and other IT professionals who want to learn more about the D3284 and consider its use in IT solutions.

Storage		Power	
Storage drives installed *	✗	Power supply unit (PSU) capacity	2214 W
Installed storage drive type *	✗	Number of power supply units	2
Total installed storage capacity *	0 TB	Redundant power supply (RPS) support	✓
Supported storage drive types *	HDD	AC input voltage	100 - 250 V
Storage drive capacity	0 GB	Weight & dimensions	
Storage drive interface	Serial ATA, Serial Attached SCSI (SAS)	Width	447 mm
Storage drive size	2.5"	Depth	933 mm
RAID levels	JBOD	Height	221 mm
Data transfer rate	12 Gbit/s	Weight	131 kg
Hot-swap drive bays	✓	Operational conditions	
Ports & interfaces		Operating temperature (T-T)	5 - 35 °C
USB connectivity	✗	Operating relative humidity (H-H)	20 - 80%
SAS host port	✓	Storage temperature (T-T)	-40 - 70 °C
Number of SAS host ports	3	Storage relative humidity (H-H)	5 - 100%
Design		Operating altitude	0 - 3048 m
Chassis type *	Rack (5U)	Non-operating altitude	0 - 12192 m
Product colour	Black	Other features	
LED indicators	✓	Compliance certificates	RoHS
Logistics data			
		Harmonized System (HS) code	84717020



5054444031699



0889488482832



889488482832

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.