

Epson Presentation Paper HiRes 120, 1067mm x 30m

Brand : Epson

Product code: C13S045289

Product name : Presentation Paper HiRes 120, 1067mm x 30m



Presentation Paper HiRes 120, 1067mm x 30m

Epson Presentation Paper HiRes 120, 1067mm x 30m:

A matte-coated, multi-purpose paper that works with dye, pigment, solvent and oil-based inks, this media is suited to the widest range of inkjet printing applications, including CAD/GIS, POS and imposition proofing, laminated and glass-mounted posters, plus advertising and tradeshow use. It provides good printability and consistent colour performance.

Presentation Paper HiRes 180 can be used outdoors when laminated.

- Matte-coated multi-purpose paper
- Supports dye, pigment, solvent and oil-based inks
- Ideal for poster, advertising and tradeshow applications
- Suits CAD/GIS, POS and imposition proofing
- Good printability and consistent colour performance

Features		Operational conditions	
Roll length *	30 m	Storage relative humidity (H-H)	10 - 80%
Roll width *	106.7 cm	Packaging data	
Size (imperial)	106.7 cm (42")	Quantity per pack	1 pc(s)
Finish type *	Matte	Package width	140 mm
Print media weight *	120 g/m²	Package depth	1120 mm
Printing media thickness	150 µm	Package height	140 mm
Paper whiteness	155	Package weight	4.82 kg
Country of origin	China	Other features	
Printing material whiteness	155%	Compatible products	Epson Stylus Pro 10600, Stylus Pro 11880, Stylus Pro 9450, Stylus Pro 9500, Stylus Pro 9600, Stylus Pro 9700, Stylus Pro 9880, Stylus Pro 9890, Stylus Pro 9900
Technical features	Epson Stylus Pro 10600, Stylus Pro 11880, Stylus Pro 9450, Stylus Pro 9500, Stylus Pro 9600, Stylus Pro 9700, Stylus Pro 9880, Stylus Pro 9890, Stylus Pro 9900		
Operational conditions		Logistics data	
Operating relative humidity (H-H)	40 - 60%	Products per pallet	50 pc(s)
Operating temperature (T-T)	15 - 30 °C	Harmonized System (HS) code	84439990
Storage temperature (T-T)	0 - 40 °C	Pallet gross width	80 cm
		Pallet gross length	120 cm
		Pallet gross height	159 cm
		Products per pallet (UK)	63 pc(s)
		Products per pallet layer	5 pc(s)



8715946491264

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.