



APC Rack PDU 2G, Switched, ZeroU, 20A/208V, 16A/230V, (7) C13 & (1) C19

Brand : APC

Product code: AP8958

Product name : Rack PDU 2G, Switched, ZeroU, 20A/208V, 16A/230V, (7) C13 & (1) C19



Rack PDU 2G, Switched, ZeroU, 20A/208V, 16A/230V, (7) C13 & (1) C19
APC Rack PDU 2G, Switched, ZeroU, 20A/208V, 16A/230V, (7) C13 & (1) C19. PDU types: Metered, Switched, Rack capacity: 0U, Mounting: Vertical. AC outlets quantity: 8 AC outlet(s), AC outlet types: C13 coupler, C19 coupler. Monitoring: Current, Power, Voltage, Outlet control: Lock-out, Recycle, Turn off, Turn on. Nominal input voltage: 230 V, Maximum current: 16 A, Load capacity: 3680 VA. Width: 56 mm, Depth: 46 mm, Height: 988 mm

Design		Power	
PDU types *	Metered, Switched	Maximum input current per phase	16 A
Rack capacity *	0U	Maximum total current draw per phase	16 A
Mounting	Vertical	Maximum power	3680 W
Ports & interfaces		Weight & dimensions	
AC outlets quantity *	8 AC outlet(s)	Width	56 mm
AC outlet types *	C13 coupler, C19 coupler	Depth	46 mm
Management features		Height	988 mm
Monitoring	Current, Power, Voltage	Weight	3.23 kg
Outlet control	Lock-out, Recycle, Turn off, Turn on	Logistics data	
Power		Total carbon footprint (kg of CO2e)	1302.31
Nominal input voltage *	230 V		
Maximum current *	16 A		
Load capacity	3680 VA		



0731304277101



731304277101

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.