

NETGEAR 10 Gigabit SR SFP+, 10pk network transceiver module
10000 Mbit/s SFP+



Brand : NETGEAR

Product code: AXM761P10-10000S

Product name : 10 Gigabit SR SFP+, 10pk

ProSafe 10GBASE-SR SFP+, 10pk

NETGEAR 10 Gigabit SR SFP+, 10pk network transceiver module 10000 Mbit/s SFP+:

- Adds 10Gigabit Ethernet "short-reach" LC fiber connectivity to the standard SFP+ interfaces
- Fits into the two built-in 10GE SFP+ interfaces of GSM72xxPS / GSM73xxS
- Fits into the 10GE SFP+ interface of the SFP+ Adapter module AX743
- Fits into standard 10Gigabit SFP+ interfaces
- LC connector
- Drives 10Gigabit Ethernet up to 300m distances with 50/125µm laser-optimized OM3 multimode fiber cables
- Drives 10Gigabit Ethernet up to 33m distances with 62.5/125µm OM1 multimode fiber cables
- Provides hot-swappable installation or removal
- 10GBaseSR fiber technology is the same for XFP and SFP+ : one Switch equipped with XFP 10GBase-SR LC connectivity can uplink to another Switch equipped with SFP+ 10GBase-SR LC connectivity using the same fiber

NETGEAR 10 Gigabit SR SFP+, 10pk. Maximum data transfer rate: 10000 Mbit/s, Interface type: SFP+, Fiber optic connector: LC. Weight: 17.1 g

Performance		Performance	
Maximum data transfer rate *	10000 Mbit/s	Maximum transfer distance	300 m
Interface type *	SFP+	Weight & dimensions	
Fiber optic connector	LC	Weight	17.1 g
SFP transceiver standard	SR	Logistics data	
		Harmonized System (HS) code	85369010



0606449087840



606449087840

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.