

Ricoh fi-7460 ADF + Manual feed scanner 600 x 600 DPI A3 Grey, White

Brand : Ricoh

Product code: PA03710-B051

Product name : fi-7460

ADF, 600 x 600 dpi, 2 x CCD, 24 bit, 60 ppm, 120 ipm (200 & 300 DPI), USB 3.0, 7.6 kg
Ricoh fi-7460. Maximum scan size: 304.8 x 5588 mm, Optical scanning resolution: 600 x 600 DPI, Output colour depth: 24 bit. Scanner type: ADF + Manual feed scanner, Product colour: Grey, White. Sensor type: Dual CCD, Light source: White LED (4x), Scan drivers: ISIS, TWAIN. Auto document feeder (ADF) input capacity: 100 sheets. Maximum ISO A-series paper size: A3, Scanning media types supported: Plain paper, ISO A-series sizes (A0...A9): A4, A8



Scanning		Weight & dimensions	
Maximum scan size *	304.8 x 5588 mm	Width	380 mm
Optical scanning resolution *	600 x 600 DPI	Depth	209 mm
Colour scanning	✓	Height	168 mm
Duplex scanning *	✓	Weight	7.6 kg
Output colour depth	24 bit	Packaging data	
Film scanning	✗	Quantity per pack	1 pc(s)
ADF scan speed (b/w, A4)	60 ppm	Package width	505 mm
ADF scan speed (colour, A4)	60 ppm	Package depth	302 mm
Duplex ADF scan speed (b/w, A4)	120 ipm	Package height	330 mm
Duplex ADF scan speed (colour, A4)	120 ipm	Package weight	9.9 kg
Black/white scanning colour modes	Grayscale, Monochrome	Packaging content	
Design		Cables included	AC, USB
Scanner type *	ADF + Manual feed scanner	Quick start guide	✓
Product colour *	Grey, White	AC adapter included	✓
Built-in display *	✓	Drivers included	✓
Performance		Bundled software	PaperStream IP, PaperStream Capture, Software Operation Panel, Error Recovery Guide, Scanner Central Admin tools, ScanSnap Manager, Scan to Microsoft SharePoint, ABBYY FineReader, 2D barcode for PaperStream
Sensor type *	Dual CCD	Sustainability	
Light source	White LED (4x)	Sustainability certificates	ENERGY STAR
Scan drivers	ISIS, TWAIN		
Input capacity			
Auto document feeder (ADF) input capacity	100 sheets		
Paper handling			
Scanning media types supported	Plain paper		
Multi feed detection	✓		
Maximum ISO A-series paper size *	A3		
ISO A-series sizes (A0...A9)	A4, A8		
Media thickness (min)	1.4 mm		
Auto Document Feeder (ADF) media weight	27 - 413 g/m²		
Maximum scan area (ADF)	304.8 x 431.8 mm		
Minimum scan area (ADF)	50.8 x 69 mm		

Ports & interfaces		System requirements	
USB port *	✓		Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 Pro, Windows 10 Pro x64, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8 x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64
USB version	3.2 Gen 1 (3.1 Gen 1)		
Socket connector type	C5		
Standard interfaces	USB 3.2 Gen 1 (3.1 Gen 1)		
Power		Windows operating systems supported	Windows Server 2008, Windows Server 2008 R2 x64, Windows Server 2008 x64, Windows Server 2012 R2 x64, Windows Server 2012 x64, Windows Server 2016 x64
Power supply type *	AC		
Power consumption (typical)	36 W		
Power consumption (standby)	0.35 W		
Power consumption (off)	0.35 W		
Power consumption (PowerSave)	1.4 W		
Input voltage	100-240 V	Server operating systems supported	
Operational conditions			
Operating temperature (T-T)		5 - 35 °C	
Operating relative humidity (H-H)		20 - 80%	
Other features			
Compliance certificates		RoHS	
Logistics data			
Country of origin		Indonesia	
Pallet gross length		121.9 cm	
Pallet gross width		101.6 cm	
Harmonized System (HS) code		8471607000	
Paper packaging weight		2.4 kg	
Metal packaging weight		0 g	
Wood packaging weight		0 g	
Plastic packaging weight		15 g	
Products per pallet (air)		24 pc(s)	
Products per pallet (sea)		40 pc(s)	
Pallet height (sea)		180 cm	
Pallet height (air)		114 cm	
Cardboard packaging weight		1.2 kg	
Foil packaging weight		15 g	
Polystyrene (EPS/EPP) packaging weight		200 g	
Glass packaging weight		0 g	



4939761308482



4058154054949

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.