

Epson Padlock Singlepack Black 35XL DURABrite Ultra Ink

Brand : Epson Product family: Padlock Product code: C13T35914020

Product name : Singlepack
Black 35XL DURABrite Ultra Ink

Singlepack Black 35XL DURABrite Ultra Ink
Epson Padlock Singlepack Black 35XL DURABrite Ultra Ink. Cartridge capacity: High (XL) Yield, Black ink type: Pigment-based ink, Black ink volume: 41.2 ml, Printing colours: Black, Quantity per pack: 1 pc(s), Black ink page yield: 2600 pages



Features		Packaging data	
Black ink type	Pigment-based ink	Package weight	10 g
Print technology	Inkjet printing	Package type	Blister
Compatibility *	- WorkForce Pro WF-4740DTWF -	Logistics data	
	- WorkForce Pro WF-4730DTWF -	Products per pallet	1800 pc(s)
	WorkForce Pro WF-4725DWF -	Pallet gross weight	0 g
	WorkForce Pro WF-4720DWF	Master (outer) case width	120 mm
Quantity per pack *	1 pc(s)	Master (outer) case length	260 mm
Black ink cartridges quantity	1	Master (outer) case height	146 mm
Black ink volume	41.2 ml	Products per master (outer) case	6 pc(s)
Black ink page yield *	2600 pages	Master (outer) case gross weight	0 g
Type *	Original	Master (outer) case GTIN (EAN/UPC)	8715946632803
Cartridge capacity	High (XL) Yield	Harmonized System (HS) code	84439990
Ink type	Pigment-based ink	Pallet weight (UK)	0 g
Printing colours *	Black	Products per pallet (UK)	1800 pc(s)
Brand compatibility *	Epson	Products per pallet layer	180 pc(s)
OEM code	C13T35914020	Products per pallet layer (UK)	180 pc(s)
Country of origin	Indonesia	Minimum order quantity	6 pc(s)
Packaging data			
Package width	113 mm		
Package depth	40 mm		
Package height	140 mm		



8715946632360



5715063385234

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.