

Epson Padlock Singlepack Yellow 35XL DURABrite Ultra Ink

Brand : EpsonProduct family: PadlockProduct code: C13T35944010

Product name : Singlepack
Yellow 35XL DURABrite Ultra Ink

Singlepack Yellow 35XL DURABrite Ultra Ink
Epson Padlock Singlepack Yellow 35XL DURABrite Ultra Ink. Colour ink type: Pigment-based ink,
Cartridge capacity: High (XL) Yield, Colour ink page yield: 1900 pages, Colour ink volume: 20.3 ml,
Printing colours: Yellow, Quantity per pack: 1 pc(s)



Features		Packaging data	
Colour ink type	Pigment-based ink	Package type	Blister
Print technology	Inkjet printing	Other features	
Compatibility *	- WorkForce Pro WF-4740DTWF - WorkForce Pro WF-4730DTWF - WorkForce Pro WF-4725DWF - WorkForce Pro WF-4720DWF	Certification	CE
Quantity per pack *	1 pc(s)	Logistics data	
Colour ink cartridges quantity	1	Products per pallet	2400 pc(s)
Colour ink volume	20.3 ml	Pallet gross weight	0 g
Colour ink page yield *	1900 pages	Master (outer) case width	120 mm
Type *	Original	Master (outer) case length	260 mm
Cartridge capacity	High (XL) Yield	Master (outer) case height	146 mm
Ink type	Pigment-based ink	Products per master (outer) case	8 pc(s)
Printing colours *	Yellow	Master (outer) case gross weight	0 g
Brand compatibility *	Epson	Master (outer) case GTIN (EAN/UPC)	8715946632858
OEM code	C13T35944010	Harmonized System (HS) code	84439990
Country of origin	Indonesia	Pallet weight (UK)	0 g
Packaging data		Products per pallet (UK)	2400 pc(s)
Package width	120 mm	Products per pallet layer	240 pc(s)
Package depth	33 mm	Products per pallet layer (UK)	240 pc(s)
Package height	145 mm	Minimum order quantity	8 pc(s)
Package weight	72 g		



8715946632414



4058154209226

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.