



APC AR3350X617 rack cabinet 42U Freestanding rack Black

Brand : APC


Product code: AR3350X617

Product name : AR3350X617

NetShelter SX 42U 750mm Wide x 1200mm Deep Enclosure Without Sides, Without Doors Black  
APC AR3350X617. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1704 kg,  
International Protection (IP) code: IP20. Weight: 161.4 kg. Product colour: Black



| Features                           |                   | Weight & dimensions         |          |
|------------------------------------|-------------------|-----------------------------|----------|
| Rack capacity *                    | 42U               | Width                       | 750 mm   |
| Type *                             | Freestanding rack | Depth                       | 1200 mm  |
| Maximum weight capacity *          | 1704 kg           | Height                      | 1991 mm  |
| Product colour                     | Black             | Weight                      | 161.4 kg |
| Frame type                         | Closed            | Mounting depth (max)        | 104.8 cm |
| Cooling type                       | Passive           | Packaging data              |          |
| International Protection (IP) code | IP20              | Package width               | 851 mm   |
| Certification                      | RoHS, REACH       | Package depth               | 1334 mm  |
| Weight & dimensions                |                   | Package height              | 2118 mm  |
| Size (imperial)                    | 48.3 cm (19")     | Package weight              | 183.2 kg |
|                                    |                   | Logistics data              |          |
|                                    |                   | Harmonized System (HS) code | 85381000 |



0731304293828



731304293828

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.