



Canon PG-40 / CL-41 ink cartridge 2 pc(s) Original Photo cyan, Photo magenta, Black, Photo yellow

Brand : Canon

Product code: 0615B051

Product name : PG-40 / CL-41



PG-40 / CL-41 multi pack, 2 ink cartridges, blister with security

Canon PG-40 / CL-41 ink cartridge 2 pc(s) Original Photo cyan, Photo magenta, Black, Photo yellow:

Canon is a leader in professional business and consumer imaging equipment and information systems. By developing innovative, high-quality business solutions Canon makes it easy to create, manage, and share images and information better, faster, and more efficiently.

To get vibrant, long-lasting prints of the highest quality, use Canon original consumables in your printers or all-in-ones. Canon consumables have been developed hand-in-hand with our sophisticated print heads to prevent smudging and clogging. Using original consumables gives you great prints and keeps your device in good shape.

Canon PG-40 / CL-41. Colour ink type: Dye-based ink, Black ink type: Pigment-based ink, Black ink volume: 16 ml, Supply type: Multi pack, Colour ink volume: 12 ml, Printing colours: Photo cyan, Photo magenta, Black, Photo yellow, Quantity per pack: 2 pc(s)



Features		Features	
Black ink type	Pigment-based ink	OEM code	0615B051
Colour ink type	Dye-based ink	Operational conditions	
Compatibility *	PIXMA iP1800, PIXMA iP2600, PIXMA MP140, PIXMA MP210, PIXMA MP470, PIXMA MX310		
Quantity per pack *	2 pc(s)		
Black ink volume	16 ml		
Colour ink volume	12 ml		
Type *	Original	Packaging data	
Printing colours *	Photo cyan, Photo magenta, Black, Photo yellow		
Brand compatibility *	Canon		
Supply type *	Multi pack	Logistics data	
		Harmonized System (HS) code	84439990



4960999974224

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.