



D-Link DES-1008D Unmanaged Fast Ethernet (10/100) Black

Brand : D-Link

Product code: DES-1008D/E

Product name : DES-1008D



DES-1008D/E - 8-Port, Fast Ethernet, IEEE 802.3x, 1Gbps  
D-Link DES-1008D. Switch type: Unmanaged. Basic switching RJ-45 Ethernet ports type: Fast Ethernet (10/100), Basic switching RJ-45 Ethernet ports quantity: 8. Full duplex. MAC address table: 1024 entries, Switching capacity: 1 Gbit/s. Networking standards: IEEE 802.3, IEEE 802.3x. Power connector: DC-in jack

| Management features                             |                         | Power over Ethernet (PoE)             |            |
|-------------------------------------------------|-------------------------|---------------------------------------|------------|
| Switch type *                                   | Unmanaged               | Power over Ethernet (PoE) *           | ✗          |
| Ports & interfaces                              |                         | Packaging data                        |            |
| Basic switching RJ-45 Ethernet ports quantity * | 8                       | Package width                         | 104 mm     |
| Basic switching RJ-45 Ethernet ports type *     | Fast Ethernet (10/100)  | Package depth                         | 158 mm     |
| Power connector                                 | DC-in jack              | Package height                        | 94 mm      |
|                                                 |                         | Package weight                        | 310 g      |
| Network                                         |                         | Technical details                     |            |
| Networking standards *                          | IEEE 802.3, IEEE 802.3x | Shipping (inner) case height          | 35 cm      |
| 10G support *                                   | ✗                       | Shipping (inner) case width           | 21.1 cm    |
| Copper ethernet cabling technology              | 100BASE-TX, 10BASE-T    | Shipping (inner) case length          | 54.3 cm    |
| Full duplex                                     | ✓                       | Shipping (inner) case net weight      | 3.96 kg    |
| Flow control support                            | ✓                       | Products per shipping (inner) case    | 20 pc(s)   |
| Auto MDI/MDI-X                                  | ✓                       | Pallet gross weight (air)             | 330.5 kg   |
| Data transmission                               |                         | Master (outer) cases per pallet (air) | 50 pc(s)   |
| Switching capacity *                            | 1 Gbit/s                | Products per pallet (air)             | 1000 pc(s) |
| MAC address table *                             | 1024 entries            | Pallet gross length                   | 110 cm     |
| Design                                          |                         | Pallet gross width                    | 120 cm     |
| Rack mounting *                                 | ✗                       | Pallet height (air)                   | 188.5 cm   |
| Stackable *                                     | ✗                       | Pallet gross weight (sea)             | 330.5 kg   |
| Product colour                                  | Black                   | Master (outer) cases per pallet (sea) | 50 pc(s)   |
| LED indicators                                  | ✓                       | Products per pallet (sea)             | 1000 pc(s) |
| Performance                                     |                         | Pallet height (sea)                   | 188.5 cm   |
| Maximum data transfer rate                      | 100 Mbit/s              | Shipping (inner) case gross weight    | 6.23 kg    |
| Mean time between failures (MTBF)               | 116186 h                | Logistics data                        |            |
| Power                                           |                         | Harmonized System (HS) code           | 85176990   |
| Input current                                   | 1 A                     |                                       |            |
| Output voltage                                  | 5 V                     |                                       |            |



0790069217715



790069217715



7900692177154



0521081065776



521081065776



0790069307287



790069307287

### Catalog Object Cloud



Disclaimer: The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.