



APC Power Cord, Locking C19 to Rewireable, 3.0m

Brand : APCProduct code: AP8759

Product name : Power Cord, Locking C19 to Rewireable, 3.0m



Power Cord, Locking C19 to Rewireable, 3.0m

APC Power Cord, Locking C19 to Rewireable, 3.0m:

This product AP8759 can free up space and secure power cords between rack-mount PDUs and attached IT equipment with the exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

APC Power Cord, Locking C19 to Rewireable, 3.0m. Cable length: 3 m. Input current: 16 A

Features		Operational conditions	
Product colour *	Black	Operating altitude	0 - 3000 m
Connector 1 gender *	Female	Non-operating altitude	0 - 15000 m
Connector 2 gender *	✗	Weight & dimensions	
Cable length *	3 m	Weight	370 g
Power		Packaging data	
Input current	16 A	Package width	230 mm
Operational conditions		Package height	230 mm
Operating temperature (T-T)	0 - 70 °C	Package weight	370 g
Storage temperature (T-T)	-20 - 70 °C	Logistics data	
Operating relative humidity (H-H)	20 - 80%	Harmonized System (HS) code	84733080
Storage relative humidity (H-H)	20 - 80%	Total carbon footprint (kg of CO2e)	116.4
Other features			
		Dimensions (WxDxH)	230 x 45 x 230 mm



0731304279822



731304279822

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.