



APC Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 16A, 230V, (21) C13 & (3) C19

Brand : APC


Product code: AP8659EU3

Product name : Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 16A, 230V, (21) C13 & (3) C19

Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 16A, 230V, (21) C13 & (3) C19
APC Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 16A, 230V, (21) C13 & (3) C19. PDU types: Metered, Metered-by-outlet, Switched, Rack capacity: 0U, Mounting: Vertical. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Power plug: IEC309. Cable length: 3 m. Monitoring: Current, Power, Voltage, Outlet control: Lock-out, Recycle, Turn off, Turn on. Nominal input voltage: 200-230 V, AC input frequency: 50 - 60 Hz, Nominal output voltage: 230 V



Design		Certificates	
PDU types *	Metered, Metered-by-outlet, Switched	Certification	EN 55022 A, EN 55024, EN 61000-3-2, EN 61000-3-3, FCC 15 A, ICES-003, PSE, UL, VCCI Class A, VDE
Rack capacity *	0U		
Mounting	Vertical		
Product colour	Black		
Ports & interfaces		Operational conditions	
AC outlets quantity *	24 AC outlet(s)	Operating temperature (T-T)	-5 - 45 °C
Power plug	IEC309	Storage temperature (T-T)	-25 - 65 °C
AC outlet types *	C13 coupler, C19 coupler	Operating relative humidity (H-H)	5 - 95%
Features		Storage relative humidity (H-H)	5 - 95%
Cable length	3 m	Operating altitude	0 - 3000 m
Management features		Non-operating altitude	0 - 15000 m
Monitoring	Current, Power, Voltage	Weight & dimensions	
Outlet control	Lock-out, Recycle, Turn off, Turn on	Width	56 mm
Power		Depth	51 mm
Nominal input voltage *	200-230 V	Height	1829 mm
AC input frequency	50 - 60 Hz	Weight	6.77 kg
Nominal output voltage	230 V	Packaging data	
Load capacity	3680 VA	Package weight	9.05 kg
Maximum input current per phase	16 A	Package width	162 mm
Maximum total current draw per phase	16 A	Package depth	117 mm
Maximum power	3680 W	Package height	2038 mm
Certificates		Logistics data	
Compliance certificates	RoHS	Total carbon footprint (kg of CO2e)	7441.92



0731304299516



731304299516

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.