



HP LaserJet 3x500-sheet Paper Feeder and Stand

Brand : HP

Product family: LaserJet

Product code: C1N63A

Product name : LaserJet
3x500-sheet Paper Feeder and
Stand

- Minimize printing interruptions and save time, using a different paper tray for each paper type. With multiple paper types ready to print, there's no need to waste time switching paper in and out of paper trays.
 - Expand your printer capacity to 2100 sheets – ideal for high-volume printing environments. A paper capacity of 2100 sheets keeps multiple users printing with fewer stops and interruptions.
 - Support a wide variety of paper types and sizes. Each tray features a media sensor that automatically adjusts settings to ensure consistent print quality.
- LaserJet 3x500-sheet Paper Feeder and Stand

[HP LaserJet 3x500-sheet Paper Feeder and Stand:](#)

High-volume printing environments that need to expand their paper capacity.
Spend less time loading paper and more time printing. Meet the printing needs of a high-volume printing environment with the 3x500-sheet paper feeder and stand for HP Color LaserJet Enterprise flow M880 MFP & HP Color LaserJet Enterprise M855 Printer




Features		Brand-specific features	
Compatibility *	HP Color LaserJet Enterprise M855 (A2W77A, A2W78A, A2W79A, D7P73A)	HP GTIN (EAN/UPC) with options	(B19) 887758643716; (BC5) 887758643709
Maximum input capacity	1500 sheets	HP GTIN (EAN/UPC)	887758643716, 887758643709
Country of origin	China	Technical details	
HP segment	Enterprise, Business	Master (outer) cases per pallet layer	
Media formats		Logistics data	
Letter	✓	Pallet dimensions (W x D x H)	856 x 838 x 676 mm
Legal	✓	Products per pallet	1 pc(s)
Weight & dimensions		Pallet dimensions (W x D x H) (imperial)	856 x 789.9 x 1351.3 mm (33.7 x 31.1 x 53.2")
Width	705 mm	Pallet weight (imperial)	44.6 kg (98.3 lbs)
Depth	700 mm	Layers per pallet	1 pc(s)
Height	389 mm	Pallet gross weight	44.7 kg
Weight	35.8 kg	Harmonized System (HS) code	84439990
Packaging data		Other features	
Package width	856 mm	Custom media sizes	
Package depth	838 mm		
Package height	676 mm		
Package weight	44.7 kg		
		UNSPSC-code	44101705



0887758643723




887758643723




8871114406482



8877586437160



4053162945135



0887111440648




887111440648



0887758643709



887758643709



0640206596855



640206596855

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "As Is" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.