



Vogel's PFW 3040 139.7 cm (55") Black

Brand : Vogel's

Product code: 7330400


Product name : PFW 3040

- 400 x 400 fitment out of the box
- Continuous smooth tilt
- Post-installation levelling
- Theft-delaying padlock

PFW 3040 Display wall mount turn & tilt

Vogel's PFW 3040 139.7 cm (55") Black:

In-room entertainment is a big part of a guest's experience. Vogel's understands that and designed the PFW 3000 Series to give everybody an outstanding AV experience. We make sure that the content is viewable from every angle. The mount's discrete padlock ensures that a HotelTV or any other display is secure on all occasions. With a maximum fitment of 400 x 400 the mount can hold a large range of displays. This, together with TÜV certification, makes this an exceptional safe and elegant solution. Vogel's PFW 3040. Maximum weight capacity: 35 kg, Minimum screen size: 99.1 cm (39"), Maximum screen size: 139.7 cm (55"), Minimum VESA mount: 100 x 100 mm, Maximum VESA mount: 400 x 400 mm. Tilt angle range: -15 - 10°, Distance to the wall (min): 11.6 cm, Distance to the wall (max): 51.1 cm. Product colour: Black



Mounting		Ergonomics	
Maximum weight capacity *	35 kg	Number of pivot points	3
Minimum screen size	99.1 cm (39")	Distance to the wall (max)	51.1 cm
Maximum screen size *	139.7 cm (55")	Distance to the wall (min)	11.6 cm
Minimum VESA mount *	100 x 100 mm	Design	
Maximum VESA mount *	400 x 400 mm	Product colour *	Black
Panel mounting interface	100 x 100, 400 x 400 mm	Certification	TÜV
Mounting type *	Wall	Weight & dimensions	
Ergonomics		Width	465 mm
Tilt adjustment	✓	Height	420 mm
Tilt angle range	-15 - 10°	Logistics data	
Turn angle	180°	Harmonized System (HS) code	85299097



8712285335181

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.