

Canon imageFORMULA ScanFront 400 Network Document Scanner

Brand : Canon

Product family:
imageFORMULA

Product code: 1255C003

Product name : Canon
imageFORMULA ScanFront 400
Network Document Scanner

A4, ADF, CMOS CIS, RGB LED, 600 x 600DPI, 45ppm, Duplex, Ethernet,USB 2.0, touchscreen, 40W
Canon imageFORMULA ScanFront 400 Network Document Scanner. Maximum scan size: 216 x 356 mm,
Optical scanning resolution: 600 x 600 DPI, ADF scan speed (b/w, A4): 45 ppm. Scanner type: ADF
scanner, Product colour: Black, White, Display: TFT. Sensor type: CMOS CIS, Daily duty cycle (max): 6000
pages, Light source: RGB LED. Auto document feeder (ADF) input capacity: 60 sheets. Maximum ISO A-
series paper size: A4, Scanning media types supported: Business Card, Plastic Card, Post Card(JPN), ISO
A-series sizes (A0...A9): A4



Scanning		Paper handling	
Maximum scan size *	216 x 356 mm	Auto Document Feeder (ADF) media weight	27 - 209 g/m ²
Optical scanning resolution *	600 x 600 DPI	Maximum scan width	21.6 cm
Colour scanning	✓	Maximum scan length	35.6 cm
Duplex scanning *	✓	Ports & interfaces	
Greyscale levels	256	USB port *	✓
ADF scan speed (b/w, A4)	45 ppm	USB version	2.0
ADF scan speed (colour, A4)	45 ppm	Standard interfaces	Ethernet, USB 2.0
Design		Network	
Scanner type *	ADF scanner	Ethernet LAN	✓
Product colour *	Black, White	Supported network protocols	TCP/IP (IPv4), DNS, DHCP, SMB, NTP, HTTP, FTP, SFTP, Secure sending (FTPS and SMTPS), WebDAV, LDAPS
Display	TFT	Power	
Display diagonal	25.6 cm (10.1")	Power supply type *	AC
Display resolution	1024 x 600 pixels	Power consumption (typical)	40 W
Touchscreen	✓	Power consumption (off)	0.5 W
Built-in display *	✓	AC input frequency	50 - 60 Hz
Performance		Input voltage	100-240 V
Sensor type *	CMOS CIS	Weight & dimensions	
Light source	RGB LED	Width	305 mm
Scan file formats	PDF, PNG, TIFF	Depth	282 mm
Daily duty cycle (max) *	6000 pages	Height	230 mm
Scan to	E-mail, FTP, Fax, USB	Weight	4.5 kg
Input capacity		Sustainability	
Auto document feeder (ADF) input capacity	60 sheets	Sustainability certificates	ENERGY STAR
Paper handling		Operational conditions	
Scanning media types supported	Business Card, Plastic Card, Post Card(JPN)	Operating temperature (T-T)	10 - 32.5 °C
Maximum ISO A-series paper size *	A4	Operating relative humidity (H-H)	20 - 80%
ISO A-series sizes (A0...A9)	A4	Other features	
Media thickness (min)	0.04 mm	Compliance certificates	RoHS

Technical details	
Panel type	TFT
Logistics data	
Harmonized System (HS) code	84716070



4528472107110

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.