




Everyday™ Mono Remanufactured Toner by Xerox compatible with HP 26X (CF226X), High capacity

Brand : Xerox

Product family: Everyday
Remanufactured

Product code: 006R03464

Product name : Everyday™
Mono Remanufactured Toner by
Xerox compatible with HP 26X
(CF226X), High capacity



Everyday™ Mono Remanufactured Toner by Xerox compatible with HP 26X (CF226X), High capacity

Everyday™ Mono Remanufactured Toner by Xerox compatible with HP 26X (CF226X), High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Mono Remanufactured Toner by compatible with HP 26X (CF226X), High capacity. Black toner page yield: 9000 pages, Printing colours: Black, Quantity per pack: 1 pc(s)

Features		Operational conditions	
Compatibility *	LaserJet Pro M402 LaserJet Pro M426	Storage relative humidity (H-H)	35 - 85%
Quantity per pack *	1 pc(s)	Weight & dimensions	
Black toner page yield *	9000 pages	Weight	1.22 kg
Type *	Compatible	Packaging data	
Printing colours *	Black	Package width	180 mm
Brand compatibility *	HP	Package depth	365 mm
Supply type *	Single pack	Package height	145 mm
Cartridge capacity	High (XL) Yield	Package weight	1.32 kg
Replacement for	HP 26X	Package type	Box
OEM code	CF226X	Other features	
Country of origin	Netherlands	Certification	RoHS, REACH SVHC, CE MARK STMC, ISO 9001:2015, ISO 14001:2015
Operational conditions		Logistics data	
Operating temperature (T-T)	17 - 25 °C	Harmonized System (HS) code	8443.99.1000
Operating relative humidity (H-H)	30 - 70%	Products per master (outer) case	6 pc(s)
Storage temperature (T-T)	0 - 35 °C		



0095205873191



095205873191



0952057415828



952057415828

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.