



APC Smart-UPS X SMX2200R2HVNC - 2200VA, 8x C13, 1x C19 outlet, USB, expandable runtime, NMC



Brand : APC

Product code: SMX2200R2HVNC

Product name : APC Smart-UPS X SMX2200R2HVNC - 2200VA, 8x C13, 1x C19 outlet, USB, expandable runtime, NMC



APC Smart-UPS X SMX2200R2HVNC - 2200VA, 8x C13, 1x C19 outlet, USB, expandable runtime, NMC
APC Smart-UPS X SMX2200R2HVNC - 2200VA, 8x C13, 1x C19 outlet, USB, expandable runtime, NMC.
UPS topology: Line-Interactive, Output power capacity: 2.2 kVA, Output power: 1980 W. AC outlet types: C13 coupler, C19 coupler, Power plug: C20 coupler, AC outlets quantity: 9 AC outlet(s). Battery technology: Sealed Lead Acid (VRLA), Battery capacity: 702 Ah, Battery recharge time: 3 h. Form factor: Rackmount/Tower, Product colour: Black, Rack capacity: 2U. Compliance certificates: RoHS, Certification: CE, EAC, EN/IEC 62040-1, EN/IEC 62040-2, GS Mark, IRAM, RCM, VDE, WEEE

Features		Design	
UPS topology *	Line-Interactive	Form factor *	Rackmount/Tower
Output power capacity *	2.2 kVA	Rack capacity	2U
Output power *	1980 W	Product colour *	Black
Waveform *	Sine	Display type	LCD
Input operation voltage (min) *	208 V	LED indicators	✓
Input operation voltage (max) *	230 V	Operational conditions	
Input frequency *	50/60 Hz	Operating temperature (T-T)	0 - 40 °C
Output operation voltage (min)	208 V	Storage temperature (T-T)	-15 - 45 °C
Output operation voltage (max)	240 V	Operating relative humidity (H-H)	0 - 95%
Output frequency	50/60 Hz	Storage relative humidity (H-H)	0 - 95%
Output frequency regulation	+/- 3 Hz	Operating altitude	0 - 3000 m
Output voltage regulation	5%	Non-operating altitude	0 - 15000 m
Surge energy rating	645 J	Certificates	
Response time	10 ms	Compliance certificates	RoHS
Emergency Power Off (EPO)	✓	Certification	CE, EAC, EN/IEC 62040-1, EN/IEC 62040-2, GS Mark, IRAM, RCM, VDE, WEEE
Noise level	55 dB	Packaging content	
Surge protection	✓	Rack mount kit	✓
Audible alarm(s)	✓	Cables included	Input power cable, USB cable
Web-based management	✓	Management card included	✓
Audible alarm modes	Battery replacement	Quick installation guide	✓
Auto-restart	✓	Weight & dimensions	
Ports & interfaces		Width	432 mm
AC outlet types	C13 coupler, C19 coupler	Depth	667 mm
Power plug	C20 coupler	Height	85 mm
AC outlets quantity	9 AC outlet(s)	Weight	37.4 kg
USB 2.0 ports quantity	1	Packaging data	
Ethernet LAN (RJ-45) ports	1	Resource CD	✓
SmartSlot	✓	Package width	596 mm
SmartConnect port	✗	Package depth	869 mm
Battery		Package height	243 mm
Battery technology	Sealed Lead Acid (VRLA)	Package weight	45.3 kg
Battery capacity	702 Ah		
Battery recharge time	3 h		
Hot-swap battery	✓		

Battery		Logistics data	
Automatic battery test	✓	Products per pallet	8 pc(s)
Cold start	✓	Harmonized System (HS) code	85078000
		Total carbon footprint (kg of CO2e)	3167.15
		Other features	
		Output voltage	230 V



0731304327738



731304327738

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.