



HP 56A Black Original LaserJet Toner Cartridge

Brand : HP

Product code: CF256A

Product name : 56A Black Original LaserJet Toner Cartridge



56A Black Original LaserJet Toner Cartridge

HP 56A Black Original LaserJet Toner Cartridge:

Ideal for business customers who want to print professional-quality black-and-white documents efficiently and at a great value.

Deliver business documents that look professional when you print with Original HP LaserJet toner cartridges. Stay productive by avoiding wasted time and supplies. These reliable cartridges are specifically designed for your HP LaserJet MFP.

HP 56A Black Original LaserJet Toner Cartridge. Black toner page yield: 7400 pages, Printing colours: Black, Quantity per pack: 1 pc(s)




**Consistent, Uninterrupted
Printing That Keeps You on Task**

Features		Sustainability	
Compatibility *	HP LaserJet M436	Total carbon footprint (kg of CO2e)	4.3
Quantity per pack *	1 pc(s)	Brand-specific features	
Black toner cartridges quantity	1	HP GTIN (EAN/UPC)	889894325457
Black toner page yield *	7400 pages	Other features	
Printing colours *	Black	Print technology	Laser
Brand compatibility *	HP	UNSPSC-code	44103103
Cartridge capacity	Standard Yield	Technical details	
OEM code	CF256A	Box contents	Toner cartridge; Recycling guide
Country of origin	China	Logistics data	
HP segment	Business	Pallet dimensions (W x D x H)	1395 x 1050 x 2533 mm
Operational conditions		Pallet dimensions (W x D x H) (imperial)	1395 x 1050 x 2532.9 mm (54.9 x 41.3 x 99.7")
Operating temperature (T-T)	10 - 30 °C	Pallet weight (imperial)	249.5 kg (550 lbs)
Operating relative humidity (H-H)	20 - 80%	Master (outer) case gross weight (imperial)	5.88 kg (13 lbs)
Storage temperature (T-T)	0 - 35 °C	Harmonized System (HS) code	84439990
Storage relative humidity (H-H)	15 - 80%	Products per master (outer) case	4 pc(s)
Weight & dimensions		Master (outer) case gross weight	5.89 kg
Width	507 mm	Master (outer) cases per pallet layer	6 pc(s)
Depth	222 mm	Master (outer) cases per pallet	42 pc(s)
Height	160 mm	Layers per pallet	7 pc(s)
Weight	690 g	Products per pallet	168 pc(s)
Packaging data		Pallet gross weight	250 kg
Package width	507 mm		
Package depth	222 mm		
Package height	160 mm		
Package weight	1.09 kg		



0889899671009



889899671009

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.