



D-Link Stacking cable f X-Stack series switch InfiniBand/fibre optic cable 0.1 m

Brand : D-Link
Product code: DEM-CB100
Product name : Stacking cable f X-Stack series switch



Stacking cable for X-Stack series switches. Suitable for: DGS-3224SRi DGS-3224SR DXS-3326GSR DXS-3350SR.L = 100 cm

D-Link Stacking cable f X-Stack series switch InfiniBand/fibre optic cable 0.1 m:

D-Link is an industry pioneer, market leader, designer and true manufacturer of networking communications and digital home electronic products. Excellence in manufacturing, innovation and a commitment to quality has allowed D-Link to produce cutting-edge, high-performance products within standard-based technologies. The company continues to offer the best value in the connectivity market today by combining high-quality products with the most affordable price point.

This 100cm 10-Gig Stacking Cable may be required when stacking more than 5 units in a stack.
D-Link Stacking cable f X-Stack series switch. Cable length: 0.1 m

Features		Logistics data	
Cable length *	0.1 m	Pallet gross weight (sea)	206 kg
InfiniBand protocol	✓	Master (outer) cases per pallet (sea)	42 pc(s)
Packaging data		Products per pallet (sea)	420 pc(s)
Package width	267 mm	Pallet height (sea)	199 cm
Package depth	317 mm	Pallet gross width	120 cm
Package height	46 mm	Pallet gross length	110 cm
Package weight	367.4 g	Harmonized System (HS) code	84733080
Logistics data		Shipping (inner) case width	33.6 cm
Shipping (inner) case net weight	3.67 kg	Shipping (inner) case length	56.2 cm
Pallet gross weight (air)	152.4 kg	Shipping (inner) case height	26.5 cm
Master (outer) cases per pallet (air)	30 pc(s)	Shipping (inner) case gross weight	4.46 kg
Products per pallet (air)	300 pc(s)	Products per shipping (inner) case	10 pc(s)
Pallet height (air)	146 cm		



0790069262463



790069262463

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.