

Epson Singlepack Blue T0549 Ultra Chrome Hi-Gloss

Brand : Epson

Product code: C13T05494010

Product name : Singlepack Blue T0549 Ultra Chrome Hi-Gloss

Singlepack Blue T0549 Ultra Chrome Hi-Gloss

Epson Singlepack Blue T0549 Ultra Chrome Hi-Gloss:

The new pigmented Ultra Chrome HI Gloss ink ensures the largest possible colour space. Especially on account of the two new ink colours red and blue. This colour combination offers an enlarged colour scale, catering for fine tuning in the case of glossy media through brightness optimisation.

Epson Singlepack Blue T0549 Ultra Chrome Hi-Gloss. Colour ink type: Pigment-based ink, Colour ink volume: 13 ml, Printing colours: Blue, Quantity per pack: 1 pc(s)



Features		Packaging data	
Colour ink type	Pigment-based ink	Package height	120 mm
Print technology	Inkjet printing	Package type	Blister
Compatibility *	- Stylus Photo R800 - Stylus Photo R1800	Other features	
Quantity per pack *	1 pc(s)	Certification	CE
Colour ink cartridges quantity	1	Logistics data	
Colour ink volume	13 ml	Pallet gross width	80 cm
Type *	Original	Pallet gross length	120 cm
Ink type	Pigment-based ink	Pallet gross height	130.5 cm
Printing colours *	Blue	Products per pallet	2400 pc(s)
Brand compatibility *	Epson	Master (outer) case width	120 mm
OEM code	C13T05494010	Master (outer) case length	260 mm
Country of origin	China	Master (outer) case height	146 mm
Colour	✓	Products per master (outer) case	48 pc(s)
Weight & dimensions		Harmonized System (HS) code	84439990
Width	246 mm	Pallet width (UK)	100 cm
Depth	116 mm	Pallet length (UK)	120 cm
Height	145 mm	Pallet height (UK)	130.5 cm
Weight	59 g	Products per pallet (UK)	2400 pc(s)
Packaging data		Products per pallet layer	240 pc(s)
Package width	145 mm	Products per pallet layer (UK)	240 pc(s)
Package depth	33 mm	Minimum order quantity	8 pc(s)



8715946356402

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.