

Brother LC1100RBWBP ink cartridge 3 pc(s) Original Cyan, Magenta, Yellow

Brand : Brother

Product code: LC1100RBWBP

Product name : LC1100RBWBP

- Each cartridge prints 325 A4 pages in accordance with ISO/IEC 24711
 - High quality genuine Brother cartridge
 - Prevents waste to save you paper, time and money
 - Using Brother LC1100 original ink cartridges protects your printer warranty
- The Brother LC1100RBWBP Cyan, Magenta and Yellow Ink Cartridges Rainbow Blister Pack. Each cartridge prints 325 A4 pages.

Brother LC1100RBWBP ink cartridge 3 pc(s) Original Cyan, Magenta, Yellow:

Ensure that replacing your genuine Brother ink cartridges is as hassle-free and affordable as possible by purchasing this LC1100RBWBP Rainbow Blister Pack. The pack contains Cyan, Yellow and Magenta cartridges, all designed to help you get the best from your Brother printer.

Brother LC1100RBWBP. Colour ink type: Pigment-based ink, Supply type: Multi pack, Colour ink page yield: 325 pages, Printing colours: Cyan, Magenta, Yellow, Quantity per pack: 3 pc(s)



Features		Weight & dimensions	
Colour ink type	Pigment-based ink	Height	125 mm
Print technology	Inkjet printing	Weight	104 g
Compatibility *	MFC-5895CW MFC-6490CW	Packaging data	
	MFC-490CW DCP-585CW	Package dimensions (WxDxH)	67 x 122 x 178 mm
	DCP-6690CW DCPJ-715W	Package weight	153 g
	MFC-5490CN MFC-6890CDW	Other features	
	MFC-790CW DCP-395CN DCP-385C	Approximate page yield (A4, colour)	325 pages
Quantity per pack *	3 pc(s)	Logistics data	
Colour ink cartridges quantity	3	Pallet gross height	16.5 cm
Colour ink page yield *	325 pages	Products per pallet	992 pc(s)
Type *	Original	Master (outer) cases per pallet	248 pc(s)
Ink type	Pigment-based ink	Layers per pallet	8 pc(s)
Printing colours *	Cyan, Magenta, Yellow	Master (outer) cases per pallet layer	31 pc(s)
Brand compatibility *	Brother	Pallet gross weight	190.9 kg
Supply type *	Multi pack	Harmonized System (HS) code	84439990
Country of origin	Malaysia	Pallet type	1200 x 1000 mm
Colour	✓		
Weight & dimensions			
Width	165 mm		
Depth	50 mm		



5014047561269

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.