



APC NetShelter AR203A - 4 Post Open Frame Rack 44U Square Holes

Brand : APC

Product code: AR203A

Product name : APC NetShelter AR203A - 4 Post Open Frame Rack 44U Square Holes

- Four-post open frame rack for straightforward access to equipment
- Industry standard (EIA-310) 19-in mounting
- High load capacity up to 2000 lb (907 kg)
- 44U design for more organization space

APC NetShelter AR203A - 4 Post Open Frame Rack 44U Square Holes

APC NetShelter AR203A - 4 Post Open Frame Rack 44U Square Holes:

APC NetShelter Open Frame offers a high-quality four-post rack for storage of industry-standard (EIA-310). Mount 19-in rack-mount hardware, which includes servers and voice, data, networking, internetworking, and APC power-protection equipment. Rack has a static load of 907 kb (2000lb) and a max equipment depth of 747 mm. The 4 post design includes square 9.5 mm holes.

APC NetShelter AR203A - 4 Post Open Frame Rack 44U Square Holes. Type: Rack frame, Product colour: Black. Weight: 40.4 kg



Features		Packaging data	
Type *	Rack frame	Package width	254 mm
Product colour *	Black	Package depth	113 mm
Rack capacity	44U	Package height	2083 mm
Certification	REACH	Package weight	40.8 kg
Weight & dimensions		Technical details	
Width	600 mm	Compliance certificates	RoHS
Depth (max)	74.7 cm	Logistics data	
Height	2130 mm	Harmonized System (HS) code	85389099
Weight	40.4 kg		



4053162266414



7313042602334



0731304260233




731304260233



0807320178941



807320178941



7426700409432

Catalog Object Cloud



Disclaimer: The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web) pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.