

Brother LC985BKBP2 ink cartridge 2 pc(s) Original Black

Brand : Brother

Product code: LC985BKBP2

Product name : LC985BKBP2

- Black cartridge prints 300 pages in accordance with ISO/IEC 24711
- High quality genuine Brother cartridge
- Prevents waste to save you paper, time and money

The Brother LC985BKBP2 Black Ink Cartridge Blister Pack. Each black cartridge prints 300 pages.



Brother LC985BKBP2 ink cartridge 2 pc(s) Original Black:

Purchase the LC985BKBP2 Ink Cartridge Blister Pack to save money on your genuine Brother cartridges. Developed to ensure you always get quality documents, you'll be protecting your printer from potential long-term damage caused by using non-genuine products.


Brother LC985BKBP2. Black ink type: Pigment-based ink, Supply type: Twin pack, Printing colours: Black, Quantity per pack: 2 pc(s), Black ink page yield: 300 pages

Features		Weight & dimensions	
Black ink type	Pigment-based ink	Depth	122 mm
Print technology	Inkjet printing	Height	177 mm
Compatibility *	DCP-J315W, MFC-J410, DCP-J125, DCP-J515W, MFC-J220	Weight	84 g
Quantity per pack *	2 pc(s)	Packaging data	
Black ink cartridges quantity	2	Package weight	150 g
Black ink page yield *	300 pages	Logistics data	
Type *	Original	Pallet gross height	16.5 cm
Ink type	Pigment-based ink	Products per pallet	1216 pc(s)
Printing colours *	Black	Master (outer) cases per pallet	304 pc(s)
Brand compatibility *	Brother	Layers per pallet	8 pc(s)
Supply type *	Twin pack	Master (outer) cases per pallet layer	38 pc(s)
Country of origin	Malaysia	Pallet gross weight	193.4 kg
Weight & dimensions		Harmonized System (HS) code	84439990
Width	60 mm	Pallet type	1200 x 1000 mm



5014047562051

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.