

Brother TN-3390 toner cartridge 1 pc(s) Original Black

Brand : Brother

Product code: TN-3390

Product name : TN-3390

- Prints 12,000 pages in accordance with ISO/IEC19752
 - High quality genuine Brother cartridge
 - Prevents waste to save you paper, time and money
- The Brother TN-3390 Black Toner Cartridge. Prints 12,000 pages.

Brother TN-3390 toner cartridge 1 pc(s) Original Black:

This genuine Brother TN-3390 High Yield Toner Cartridge is capable of printing up to 12,000 pages, producing brilliant results from the very first to the last page you print.
Brother TN-3390. Black toner page yield: 12000 pages, Printing colours: Black, Quantity per pack: 1 pc(s)




Features		Weight & dimensions	
Compatibility *	MFC-8950DWT DCP-8250DN HL-6180DW HL-6180DWT MFC-8950DW	Weight	760 g
Quantity per pack *	1 pc(s)	Dimensions (WxDxH)	290 x 132 x 81 mm
Black toner cartridges quantity	1	Packaging data	
Black toner page yield *	12000 pages	Package dimensions (WxDxH)	362 x 201 x 149 mm
Type *	Original	Package weight	1.28 kg
Printing colours *	Black	Other features	
Brand compatibility *	Brother	Print technology	Laser printing
Supply type *	Single pack	Logistics data	
Cartridge return & recycling	✓	Harmonized System (HS) code	84439990
Cartridge capacity	High (XL) Yield	Master (outer) cases per pallet layer	5 pc(s)
Country of origin	China	Master (outer) cases per pallet	50 pc(s)
Weight & dimensions		Layers per pallet	10 pc(s)
Width	203 mm	Products per pallet	150 pc(s)
Depth	152 mm	Pallet gross height	18 cm
Height	361 mm	Pallet gross weight	198.5 kg
		Pallet type	1200 x 1000 mm



5711045842207



4977766708920



4977766705820

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.