

Targus CityGear 39.6 cm (15.6") Backpack Black

Brand : Targus

Product code: TCG661GL

Product name : CityGear

- Versatile laptop bag to carry your tech; allowing you to carry as a briefcase or a backpack, depending on your day
- Detachable shoulder straps and retractable handle for quick switch from backpack to briefcase
- Dome Protection System; shock-absorbing layers dissipate any impact pressure on laptop & tablet inside
- Laptop & Tablet compartments
- Multi-Fit compatibility: Fits 14-15.6" laptops
- Comfort-padded grab handle and padded shoulder straps
- Zipped mesh pockets and compartments for smart organisation
- Trolley strap

CityGear 14-15.6" Convertible Laptop Backpack - Black

Targus CityGear. Case type: Backpack, Maximum screen size: 39.6 cm (15.6"), Carrying handle(s), Shoulder strap. Weight: 770 g. Surface coloration: Monochromatic



Features		Weight & dimensions	
Surface coloration	Monochromatic	Depth	322 mm
Maximum screen size *	39.6 cm (15.6")	Height	458 mm
Case type *	Backpack	Weight	770 g
Material *	Nylon, Polyester	Package width	123 mm
Product main colour *	Black	Package depth	322.9 mm
Integrated compartment(s)	✓	Package height	460 mm
Tablet compartment	✓	Package weight	1.01 kg
Brand compatibility *	Any brand	Logistics data	
Front pocket	✓	Products per pallet	50 pc(s)
Carrying handle(s)	✓	Harmonized System (HS) code	84733080
Shoulder strap	✓	Master (outer) case width	475 mm
Protection features	Shock resistant	Master (outer) case length	750 mm
Country of origin	China	Master (outer) case height	340 mm
Quantity	1	Master (outer) case gross weight	6.26 kg
Weight & dimensions		Products per master (outer) case	5 pc(s)
Width	120 mm		



5051794027990



0092636339036



092636339036

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.