

Targus DOCK315EUZ laptop dock/port replicator USB 3.2 Gen 1 (3.1 Gen 1) Type-A + Mini DisplayPort 1.2 Black

Brand : Targus

Product code: DOCK315EUZ

Product name : DOCK315EUZ

- Supports single 5K and dual 4K UHD HDR @ 60 Hz video via two DisplayPort™ ports
 - Included 100W AC Power Adapter
 - 1x USB 3.2 Gen 2 Type-C 10 Gbps upstream facing port
 - 1 m USB-C detachable host cable with USB-C to USB-A tethered adapter for USB-A only host laptops
 - 1x USB 3.2 Gen 2 Type-C 10 Gbps downstream facing port
 - 3x USB 3.2 Gen 1 Type-A downstream facing ports
 - Gigabit Ethernet port
 - 3.5mm combo Audio In/Out port
 - Integrated lock slot accommodates standard security locks to safeguard equipment (compatible with Targus PA410, ASP8 and ASP9 series cable locks)
- USB 3.2G1, USB-A, USB-C, 65W, DP
- Targus DOCK315EUZ. Host interface: USB 3.2 Gen 1 (3.1 Gen 1) Type-A + Mini DisplayPort 1.2, USB Power Delivery up to: 65 W. Product colour: Black, Cable lock slot type: Kensington, Hub interfaces: 3.5mm, DisplayPort, RJ-45, USB 3.2 Gen 1 (3.1 Gen 1) Type-C, USB Type-C. Power supply: 65 W, Output voltage: 20 V. Width: 165 mm, Depth: 8.3 mm, Height: 2.9 mm. Quantity per pack: 1 pc(s)



Ports & interfaces		Performance	
Host interface *	USB 3.2 Gen 1 (3.1 Gen 1) Type-A + Mini DisplayPort 1.2	Product colour *	Black
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	3	Hub interfaces	3.5mm, DisplayPort, RJ-45, USB 3.2 Gen 1 (3.1 Gen 1) Type-C, USB Type-C
USB 3.2 Gen 1 (3.1 Gen 1) Type-C ports quantity	1	Plug and Play	✓
USB Power Delivery (USB PD)	✓	Country of origin	Taiwan
USB Power Delivery revision	4.0	Power	
USB Power Delivery up to	65 W	Power supply	65 W
DisplayPorts quantity	2	Output voltage	20 V
Combo headphone/mic port	✓	Weight & dimensions	
DC-in jack	✓	Width	165 mm
Performance		Depth	8.3 mm
Card reader integrated *	✗	Height	2.9 mm
Cable lock slot type	Kensington	Weight	290 g
		Packaging data	
		Quantity per pack	1 pc(s)



5051794034608

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.