



Canon WA10 Ethernet / WLAN

Brand : Canon

Product code: 2999C003

Product name : WA10



Network adapter f / DR-C230/C240/M140/M160II/M260/M1060

[Canon WA10 Ethernet / WLAN:](#)

Enabling scanning directly over the network with Canon's USB scanners.

A simple way to expand your office's scanning capability

Network adapters that enable users to share access to Canon's imageFormula scanners across multiple computers. Delivers enhanced mobile scanning options and works seamlessly with a choice between a wired or wireless connection.

Expand access

Consolidate management of scanners in an office on to a single wired or wireless network.

Push scanning

Streamline the scanning process by undertaking jobs with one button press on the scanner.

Mobile control

Perform scanning functions from mobiles and smart devices without using a computer.

Canon WA10. Connectivity technology: Wired & Wireless, Host interface: USB Type-C, Interface: Ethernet / WLAN. Top Wi-Fi standard: Wi-Fi 4 (802.11n), Wi-Fi band: Single-band (2.4 GHz). Product colour: Black

Ports & interfaces		Network	
Connectivity technology *	Wired & Wireless	Security algorithms	WEP, WPA-PSK, WPA2-PSK, WPS
Host interface *	USB Type-C	Design	
Interface *	Ethernet / WLAN	Component for *	PC
Ethernet LAN (RJ-45) ports	1	Product colour	Black
USB ports quantity	1	Internal *	✗
USB version	2.0	LED indicators	✓
Network		Operational conditions	
Networking standards *	IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IEEE 802.3, IEEE 802.3ab, IEEE 802.3u	Operating temperature (T-T)	10 - 35 °C
Ethernet LAN	✓	Operating relative humidity (H-H)	20 - 85%
Ethernet interface type	Gigabit Ethernet	Weight & dimensions	
Ethernet LAN data rates	10,100,1000 Mbit/s	Width	116 mm
Cabling technology	10/100/1000BaseT(X)	Depth	93.6 mm
Wi-Fi	✓	Height	28.8 mm
Wi-Fi band	Single-band (2.4 GHz)	Weight	179 g
Top Wi-Fi standard	Wi-Fi 4 (802.11n)	Logistics data	
Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)	Harmonized System (HS) code	85176990



4528472108544

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.