



APC BVX900LI-GR uninterruptible power supply (UPS) Line-Interactive 0.9 kVA 480 W 2 AC outlet(s)

Brand : APC

Product code: BVX900LI-GR

Product name : BVX900LI-GR




900VA, 230V, AVR, 2x Schuko Sockets, Black

APC BVX900LI-GR. UPS topology: Line-Interactive, Output power capacity: 0.9 kVA, Output power: 480 W. AC outlet types: Type F, Power plug: Type F, AC outlets quantity: 2 AC outlet(s). Battery technology: Sealed Lead Acid (VRLA), Battery capacity: 9 Ah, Battery voltage: 12 V. Form factor: Compact, Product colour: Black, International Protection (IP) code: IP20. Certification: CB, CE, EN/IEC 62040-1, EN/IEC 62040-2



Features		Battery	
UPS topology *	Line-Interactive	Battery voltage	12 V
Output power capacity *	0.9 kVA	Battery life (max)	2 year(s)
Output power *	480 W	Battery recharge time	8 h
Waveform *	Sine	Cold start	✓
Input operation voltage (min) *	170 V	Design	
Input operation voltage (max) *	280 V	Form factor *	Compact
Input frequency *	50/60 Hz	Product colour *	Black
Output operation voltage (min)	230 V	LED indicators	✓
Output operation voltage (max)	230 V	International Protection (IP) code	IP20
Output frequency	50/60 Hz	Operational conditions	
Output frequency regulation	0.5 Hz	Operating temperature (T-T)	0 - 40 °C
Output voltage regulation	10%	Storage temperature (T-T)	-15 - 40 °C
Automatic Voltage Regulation (AVR)	✓	Operating relative humidity (H-H)	0 - 95%
Surge energy rating	273 J	Operating altitude	0 - 3000 m
Response time	6 ms	Non-operating altitude	0 - 3000 m
Input power factor	0.53	Certificates	
Noise level	40 dB	Certification	CB, CE, EN/IEC 62040-1, EN/IEC 62040-2
Surge protection	✓	Packaging content	
Audible alarm(s)	✓	Cables included	Input power cable
Audible alarm modes	Alarm when on battery, Battery replacement, Low battery alarm, Overload alarm	Management card included	✗
Ports & interfaces		Manual	✓
AC outlet types	Type F	Weight & dimensions	
Power plug	Type F	Width	120 mm
AC outlets quantity	2 AC outlet(s)		

Ports & interfaces		Weight & dimensions	
SmartSlot	×	Depth	355 mm
SmartConnect port	×	Height	160 mm
Battery		Weight	6 kg
		Packaging data	
		Package width	197 mm
Battery technology	Sealed Lead Acid (VRLA)	Package depth	430 mm
Battery capacity	9 Ah	Package height	250 mm
		Package weight	6.5 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0731304404590



731304404590

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.