



APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 800W x 1200D mm


Brand : APC

Product code: ER8222


Product name : Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 800W x 1200D mm

Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 800W x 1200D mm

APC Easy Rack, 42U, Black, With Roof, Castors, Feet, 4 Brackets, and Side Panels, No Bottom, 1991H x 800W x 1200D mm. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1199.75 kg, Key lock, Adjustable feet, Castor wheels. Weight: 135 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	42U	Size (imperial)	48.3 cm (19")
Type *	Freestanding rack	Width	800 mm
Maximum weight capacity *	1199.75 kg	Depth	1200 mm
Maximum weight capacity (rolling)	599.65 kg	Height	1991 mm
Product colour	Black	Weight	135 kg
Side panels included	✓	Mounting depth (min)	24.2 cm
Side panel style	Blind	Mounting depth (max)	104.1 cm
Key lock	✓	Packaging data	
Back door key lock	✓	Package width	1250 mm
Front door key lock	✓	Package depth	850 mm
Side panel key lock	✓	Package height	2120 mm
Adjustable feet	✓	Package weight	144 kg
Castor wheels	✓	Technical details	
Preassembled	✓	Total carbon footprint (kg of CO2e)	436.94
Certification	EIA-310E, UL 2416, UL 60950-1	Logistics data	
		Harmonized System (HS) code	85381000



0731304427865



731304427865

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.