




Lenovo 4XC7A08236 network card Internal Ethernet 10000 Mbit/s

Brand : Lenovo

Product code: 4XC7A08236

Product name : 4XC7A08236



ThinkSystem Broadcom 57416 10GBASE-T 2-port OCP Ethernet Adapter


[Lenovo 4XC7A08236 network card Internal Ethernet 10000 Mbit/s:](#)

The Broadcom 57416 10Gb BASE-T Ethernet Adapters are dual-port 10GBASE-T adapters that are fully compliant with the IEEE 802.3an standard and provide a low-cost solution for 10 Gb Ethernet using copper wiring.

This product guide provides essential presales information to understand the Broadcom adapters and their key features, specifications, and compatibility. This guide is intended for technical specialists, sales specialists, sales engineers, IT architects, and other IT professionals who want to learn more about the adapters and consider their use in IT solutions.

Lenovo 4XC7A08236. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 10000 Mbit/s

Ports & interfaces		Design	
Connectivity technology *	Wired	Certification	CE/European Union EN60950-1 UL/USA UL60950-1 CTUVus UL Canada: CSA 22.2 No. 950 Taiwan: CNS14336 Class A EN55022:2010 + *AC:2011 Class A EN55024 Class A FCC CFR47, Part 15 Class A Canada: ICES-003 Class A Australia, New Zealand: EN 5022:2010 + *AC:2011 Taiwan: BSMI CNS13438 Class A South Korea: MIC RRL KN22 Class A South Korea: KN24 (ESD) Japan: VCCI V-3 04/2014 EN55024:2010 Air/Direct discharge
Host interface *	PCI Express		
Interface *	Ethernet		
Ethernet LAN (RJ-45) ports	2		
PCI version	3.0		
Network			
Maximum data transfer rate *	10000 Mbit/s		
Networking standards *	IEEE 802.3ab, IEEE 802.3an		
Ethernet LAN	✓		
Ethernet interface type	10 Gigabit Ethernet		
Ethernet LAN data rates	1000,10000 Mbit/s		
Cabling technology	10/100/1000BaseT(X)		
Design		System requirements	
Component for *	Server	Windows operating systems supported	✓
Internal *	✓	Linux operating systems supported	✓
Antenna	✗		
Form factor	OCP 3.0		
		Operational conditions	
		Storage temperature (T-T)	-40 - 65 °C
		Storage relative humidity (H-H)	5 - 95%
		Weight & dimensions	
		Width	76 mm
		Depth	115 mm



0889488497294



889488497294

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.